VLFG-630+

 50Ω DC to 630 MHz

Generic photo used for illustration purposes only

CASE STYLE: FF704

The Big Deal

- Good power handling, 3.5 W
- Temperature stable
- Rugged unibody construction
- Good rejection, 46 dB typical

Product Overview

VLFG-630+ is a 50Ω low pass filter built in rugged unibody construction. Covering DC-630 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VLFG-630+ offer low insertion loss, and good power handling capability. It handles up to 3.5W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages		
Low passband insertion loss	Suitable for high performance application.		
3.5 W Power handling	Supports a range of system power requirements.		
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.		

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Low Pass Filter

DC to 630 MHz 50Ω

VLFG-630+



Generic photo used for illustration purposes only CASE STYLE: FF704

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Features

- Low loss, 1.5 dB typical
- · Good rejection 46 dB typical
- · Good power handling, 3.5 W
- Temperature stable
- Connectorized package
- Rugged unibody construction

Applications

- Harmonic Rejection
- VHF/UHF transmitters / receivers
- · Military radar applications
- Test and measurement
- Telecommunications & broadband wireless applications
- Satcom modems

Functional Schematic



Electrical Specifications at 25°C

Pa	rameter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Insertion Loss	DC-F1	DC - 630	_	1.5	2.1	dB
Pass Band	Freq. Cut-Off	F2*	780	_	3.0	_	dB
	Return Loss	DC-F1	DC - 630	_	14	_	dB
		F3-F4	1050 - 1500	20	50	_	dB
Stop Band	Rejection Loss	F4-F5	1500 - 3800	35	46	_	dB
		F5-F6	3800 - 8500	_	21	_	dB

In Application where DC voltage is present at either input or output port, DC blocks are required.

^{*} Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.


Maximum Ratings			
Operating Temperature	-55°C to 125°C		
Storage Temperature	-55°C to 125°C		
RF Power Input*	3.5 W max.@25°C		


^{*}Passband rating, derate linearly to 0.8 W at 125°C ambient Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C


Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.13	35.14
100	0.27	24.57
500	0.94	19.82
600	1.30	15.22
630	1.43	14.66
780	2.74	19.89
800	3.37	18.02
910	20.78	2.91
950	30.19	1.91
1000	41.66	1.32
1050	52.12	1.00
1500	53.83	0.38
2000	47.40	0.32
2400	46.22	0.30
3000	48.23	0.26
3800	64.87	0.24
4000	63.26	0.25
5000	27.91	0.75
7000	33.95	0.43
8500	32.39	2.06

Typical Frequency Response









Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch)

wt	Ε	D	В
grams	.312	1.43	.410
10	7 92	36.32	10 41

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

