Coaxial ow Pass Filter

DC to 650 MHz (40 dB Isolation up to 20 GHz) 50Ω

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W max. at 25°C
*Passband rating, derate linearly to a	

Features

- very good isolation, 40 dB up to 20 GHz
- · 21 sections
- excellent power handling, 10W
- temperature stable LTCC internal structure
- re-entry frequency > 20 GHz
- rugged unibody construction
- protected by US patent 6,943,646

Applications

- · harmonic rejection
- transmitters/receivers
- · lab use
- · test instrumentation




CASE STYLE: FF1118

Connectors	Model
SMA	VLFX-650+
SMA	VLFX-650

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Outline Dimensions (inch)

			• mm
В	D	E	wt.
.410	2.67	.312	grams
10.41	67.82	7.92	17.0


Low Pass Filter Electrical Specifications @ 25°C

MODEL NO.	PASSBAND (MHz)	Fco, MHz Nom		BAND (MHz) oss, dB)	VSW	R (:1)	NO. OF SECTIONS
	(Loss < 1.2dB) Max.	(Loss 3 dB) Typ	F20 Min.	F40 Typ.	Stopband Typ.	Passband Typ.	
VLFX-650 (+)	DC-650	1025	1275	1450-20000	10	1.2	21

Typical Frequency Response





Functional Schematic



Typical Performance Data @ 25°C

VSWR (:1)	Insertion Loss (dB)	Frequency (MHz)
1.08	0.29	50
1.13	0.39	200
1.11	0.54	400
1.20	0.89	650
1.27	1.22	800
1.20	1.57	900
1.32	2.92	1025
2.42	9.11	1125
6.45	31.28	1275
16.47	41.47	1450
24.07	53.44	1575
41.80	51.81	2000
89.22	82.03	3000
52.93	82.92	5000
48.67	75.09	7500
7.09	99.20	10000
14.19	60.25	12500
6.64	69.31	15000
19.28	61.54	17500
11.14	60.47	20000
VLFX-650 VSWR		VLFX-650 INSERTION LOSS
	100	20
	100 -	





Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

BEV E M151121 VLFX-650 EDU-0399 ED-11930A/11 URJ/AD/CP 161015 Page 1 of 1

