Wideband, DC Pass Directional Coupler zcpc20-01203-S+

20dB Up to 20W 1 to 20 GHz 50Ω

The Big Deal

- Wideband, 1 to 20 GHz
- Excellent Coupling Flatness, ±0.26 dB typ.
- Power Handling up to 20W



CASE STYLE: HT2679-N

Product Overview

The Mini-Circuits ZCDC20-01203-S+ wideband directional coupler offers exceptional performance operating over 1 to 20 GHz. This coupler has excellent coupling flatness, good directivity, and power handling. It is ideal for lab testing applications as well as for power monitoring over wide bands, among other applications.

Key Features

Feature	Advantages
Wide bandwidth	With a bandwidth spanning 1 to 20 GHz, ZCDC20-01203-S+ coupler is ideal for most lab testing applications, avoiding the need to switch components for different frequency bands.
Excellent Directivity • 19 dB typ. up to 20 GHz	High directivity allows sampling of input powers with minimal detrimental effects due to input mismatches.
Excellent coupling flatness, ±0.26 dB typ	Excellent coupling flatness over the entire frequency range minimizes the need for compensation circuits in most cases.
Good Return Loss (In & Out) • 21 dB typ. up to 20 GHz	Good return loss over 1 to 20 GHz minimizes undesired reflections and resulting ampli- tude ripple.

- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Notes

Wideband, DC Pass **Directional Coupler**

Up to 20W 50Ω 20dB


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Supplied Termination*	1W
DC Current	0.63A
P 11 17	7.0 F 5 1 1

Permanent damage may occur if any of these limit ' up to 25°C, derates linearly to 325mW at 100°C.

Coaxial Connections

INPUT	IN
OUTPUT	OUT
COUPLED	CPL
TERMINATION (50Ω) INCLUDED	_



	Outli	ne D	imen	sion	s (in	ch)
А	В	С	D	E	F	G
3.50	0.70	0.50	1.181	1.138	0.122	0.25
88.90	17.78	12.70	30.00	28.91	3.10	6.35
н	J	к	L	M	N	wt
0.102	1.00	1.50	0.303	0.098	0.2	grams
2.59	25.40	38.10	7.70	2.5	5.08	80

Features

1 to 20 GHz

- Wide frequency range, 1 to 20 GHz
- Good coupling flatness, ±0.26 dB typ.
- Good directivity, 19 dB typ. up to 20 GHz
- · Good return loss, 21 dB typ. up to 20 GHz
- DC current pass through input to output

Applications

- 5G
- Mobile
- Fixed satellite
- Lab use

ZCDC20-01203-S+



CASE STYLE: HT2679-N

Connectors Model

SMA Female

ZCDC20-01203-S+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


Parameter	Frequency (GHz)	Min.	Тур.	Max.	Units	
Operating Frequency		1		20	GHz	
Nominal Coupling	1 - 20	-	20±1.35	-	dB	
Coupling Flatness (±)	1 - 20	-	±0.26	±0.35	dB	
Mainline Loss ¹	1 - 8	-	0.3	0.7	dB	
	8 - 20	-	0.6	1.0		
Directivity	1 - 8	17	33	-	dB	
	8 - 20	14	25	-		
Return Loss (In & Out)	1 - 8	17.6	38	-	dB	
	8 - 20	16.5	29	-		
Return Loss (Coupling)	1 - 8	17.6	33	-	dB	
	8 - 20	16.5	26	-		
Input Power ²	1 - 20	-	-	20	W	


1. Mainline loss includes coupling loss

2. up to 25°C, derates linearly to 18W at 100°C.

Typical Performance Data							
Frequency (MHz)	Mainline Loss¹ (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	In	Return Loss (dB) Out	Cpl	
1000	0.19	19.29	46.27	69.07	39.54	37.70	
2000	0.24	19.42	37.49	39.42	47.03	36.53	
4000	0.31	19.29	39.59	40.95	41.55	34.67	
6000	0.37	19.34	34.12	38.68	38.68	27.80	
8000	0.43	19.31	22.95	35.10	37.44	25.82	
12000	0.53	19.29	26.49	38.40	40.68	23.15	
14000	0.59	19.33	21.62	23.84	24.34	18.92	
16000	0.64	19.36	30.76	22.19	21.71	18.81	
18000	0.67	19.28	19.21	22.36	22.73	23.16	
20000	0.73	19.49	30.04	21.06	21.60	24.52	

1. Mainline loss includes coupling loss





A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collective), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp


REV. OR ECO-004028 ZCDC20-01203-S+ CM/RS/CP 200909 Page 2 of 2



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Electrical Schematic DIRECTIONAL COUPLER (DC THRU) DC+RF DC+RF INCLUDED





Notes