

VXHF-482M+

 50Ω

4800 to 9000 MHz

The Big Deal

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Temperature stable up to 100°C



Generic photo used for illustration purposes only CASE STYLE: FF704

Product Overview

Mini-Circuits' VXHF-482M+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

Key Features

Feature	Advantages	
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range.	
Enables stable integration of wideband amplifiers	Because reflectionless filters maintain good impedance in the stop band; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions.	
Operating temperature up to 100°C	Suitable for operation close to high power components.	
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.	

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

ligh Pass Filter

4800 to 9000 MHz 50Q

VXHF-482M+



Generic photo used for illustration purposes only CASE STYLE: FF704

> Connectors SMA-M/F

Model VXHF-482M+

Electrical Specifications at 25°C

Electrical openingations at 20 C							
Pa	rameter	F# Frequency (MHz) Min. Typ. Ma		Max.	Unit		
Rejection	DC-F1	DC- 2400	16	37	-	dB	
	hejection	F1-F2	2400 - 3600	14	36	-	dB
Stop Band	Freq. Cut-Off	F3	4390	-	3.0	-	dB
	VSWR	DC-F1	DC - 2400	-	1.3	-	:1
		F1-F2	2400 - 3600		1.3		:1
	Insertion Loss	F4-F6	4800 - 9000	-	1.5	3.0	dB
Pass Band	s Band VSWR	F4-F5	4800 - 6000	-	2.0	-	:1
VOVIN	F5-F6	6000 - 9000	_	3.0	_	-1	

Absolute Maximum Ratings³


Parameter	Ratings		
Operating Temperature	-55°C to +100°C		
Storage Temperature	-55°C to +100°C		
RF Power Input, Passband (F4-F6) ¹	1.3W at 25°C		
RF Power Input, Stopband (DC-F4) ²	1.6W at 25°C		


ESD rating

Human body model (HBM): Class 2(Pass 2000 V) in accordance with ANSI/ESD STM 5.1-2001

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	60.75	1.24
100	50.25	1.25
300	35.74	1.26
450	30.56	1.27
1000	28.54	1.29
2400	30.21	1.27
2500	31.98	1.29
3000	30.01	1.25
3600	27.73	1.11
4000	5.76	1.16
4335	3.00	1.16
4390	2.78	1.14
4800	1.90	1.10
4900	1.79	1.15
5000	1.70	1.21
6000	1.55	1.82
7000	1.62	2.21
8000	1.36	1.96
8500	1.08	1.62
9000	0.78	1.34






Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Temperature stable up to 100°C
- Protected by US Patents 8,392,495; 9,705,467, additional patent pending
- Protected by China Patent 201080014266.1
- Protected by Taiwan Patent I581494


Applications

- Wi-Fi
- WiMax
- Microwave Radio
- · Military & Space

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

 $^{^1}$ Passband rating derates linearly to 0.6W at 100°C ambient 2 Stopband rating derates linearly to 0.8W at 100°C ambient


³ Permanent damage may occur if any of these limits are exceeded



Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch)

wt	Ε	D	В
grams	.312	1.43	.410
10	7.92	36.32	10.41

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp