Coaxial Reflectionless

Low Pass Filter

VXLF-172H+

 50Ω DC to 2000 MHz

The Big Deal

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent power handling
- Temperature stable up to 100°C



Generic photo used for illustration purposes only CASE STYLE: FF704

Product Overview

Mini-Circuits' VXLF-172H+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

Key Features

| Feature | Advantages |
|---|---|
| Easy integration with sensitive reflective components, e.g. mixers, multipliers | Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range. |
| Enables stable integration of wideband amplifiers | Because reflectionless filters maintain good impedance in the stop band; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions. |
| Excellent power handling | High power handling extends the usability of these filters to the transmit path for interstage filtering. |
| Operating temperature up to 100°C | Suitable for operation close to high power components. |
| Connectorized package | The connectorized package is easy to interface with other devices and well suited for test setups. |

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Low Pass Filter

50Q DC to 2000 MHz

VXLF-172H+



Generic photo used for illustration purposes only CASE STYLE: FF704

| Connectors | Model | | |
|------------|-------------|--|--|
| SMA-M/F | VXI F-172H+ | | |

Electrical Specifications at 25°C

| Pa | arameter | F# | Frequency (MHz) | Min. | Тур. | Max. | Unit |
|--------------------------|-------------------|-------|-----------------|------|------|------|------|
| | Insertion Loss | DC-F1 | DC - 2000 | - | 1.7 | 3.4 | dB |
| Pass Band | Frequency Cut-off | F2 | 2350 | - | 3.0 | - | dB |
| | VSWR | DC-F1 | DC-2000 | - | 1.4 | - | :1 |
| Rejection Stop Band VSWR | Dejection | F3-F4 | 3600 - 3800 | 10 | 28 | - | dB |
| | Rejection | F4-F5 | 3800 - 11000 | 26 | 47 | - | dB |
| | VSWR | F3-F4 | 3600 - 3800 | - | 1.4 | - | :1 |
| | | F4-F5 | 3800 - 11000 | - | 1.7 | _ | :1 |

Absolute Maximum Ratings³

| Parameter | Ratings | | |
|---|-----------------|--|--|
| Operating Temperature | -55°C to +100°C | | |
| Storage Temperature | -55°C to +100°C | | |
| RF Power Input, Passband (DC-F1) ¹ | 7.9W at 25°C | | |
| RF Power Input, Stopband (F3-F5) ² | 1.58W at 25°C | | |


- Passband rating derates linearly to 3.9W at 100°C ambient
- ² Stopband rating derates linearly to 0.75W at 100°C ambient ³ Permanent damage may occur if any of these limits are exceeded


ESD rating

Human body model (HBM): Class 1A (Pass 250 V) in accordance with ANSI/ESD 5.1-2001

Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|--------------------|------------------------|--------------|
| 10 | 1.07 | 1.15 |
| 100 | 1.10 | 1.15 |
| 300 | 1.18 | 1.20 |
| 600 | 1.33 | 1.28 |
| 1000 | 1.61 | 1.37 |
| 2000 | 2.48 | 1.16 |
| 2350 | 3.01 | 1.09 |
| 2500 | 3.35 | 1.15 |
| 3000 | 5.55 | 1.24 |
| 3600 | 19.98 | 1.22 |
| 3610 | 20.64 | 1.22 |
| 3720 | 30.58 | 1.27 |
| 3800 | 42.52 | 1.30 |
| 4000 | 52.23 | 1.41 |
| 5000 | 46.04 | 1.57 |
| 6000 | 35.46 | 1.32 |
| 7000 | 37.69 | 1.10 |
| 9000 | 51.09 | 1.28 |
| 10000 | 54.46 | 1.23 |
| 11000 | 57.94 | 1.15 |






Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent stopband rejection, 47 dB typ.
- Temperature stable, up to 100°C
- Protected by US Patents 8,392,495; 9,705,467, additional patent pending
- Protected by China Patent 201080014266.1
- Protected by Taiwan Patent I581494


Applications

- Cellular, PCS
- GPS
- · Radio astronomy
- Telemetry

Functional Schematic



Typical Frequency Response



+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

| PORT - 1 | SMA-Male |
|----------|------------|
| PORT - 2 | SMA-Female |

Outline Drawing



Outline Dimensions (inch)

| В | D | Е | wt. |
|-------|-------|------|-------|
| .410 | 1.43 | .312 | grams |
| 10 41 | 36.32 | 7 92 | 10 |

Note: Please refer to case style drawing for details

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Firms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp