

Coaxial Directional Coupler

50Ω

0.5 to 500 MHz

ZDC-10-1+
ZDC-10-1



CASE STYLE: M22

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Coaxial Connections

INPUT	3
OUTPUT	2
COUPLED	1

Features

- excellent directivity, 32 dB typ.
- excellent insertion loss, 0.65 dB typ.
- rugged shielded case

Applications

- VHF/HF
- instrumentation
- communication receivers & transmitters

Connectors	Model	Price	Qty.
BNC	ZDC-10-1(+)	\$44.95 ea.	(1-9)
BRACKET (OPTION"BR")		\$5.00	(1+)
BRACKET (OPTION"BR")		\$1.50	(1+)

+ RoHS compliant in accordance
with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site
for RoHS Compliance methodologies and qualifications.

Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT (W)	
			L		M		U		L		M		U				
	f_L - f_U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.		Min.	Typ.
0.5-500	11.5±0.5	±0.6	0.85	1.3	0.65	1.0	0.85	1.3	32	25	32	25	22	15	1.2	1.5	3.0


L = low range [f_L to 10 f_L] M = mid range [10 f_L to $f_U/2$] U = upper range [$f_U/2$ to f_U]

1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		Cpl
				In	Out	
0.50	0.79	11.64	51.25	23.85	19.63	19.66
0.90	0.70	11.56	50.03	27.29	21.30	21.28
4.00	0.56	11.44	49.98	34.05	24.12	23.94
38.00	0.59	11.48	46.48	35.54	23.96	23.10
94.00	0.61	11.51	41.48	32.20	23.33	20.84
160.00	0.62	11.54	38.35	28.76	22.29	18.21
210.00	0.67	11.63	36.91	26.97	21.43	16.63
275.00	0.74	11.71	34.57	25.19	20.29	15.00
400.00	0.94	11.85	26.91	22.30	18.40	13.06
500.00	1.05	11.79	20.87	19.79	17.45	12.48




Outline Drawing




Outline Dimensions (inch)

A	B	C	D	E	F	G	H
2.25	1.38	1.24	.50	.150	3.100	.138	1.238
57.15	35.05	31.50	12.70	3.81	78.74	3.51	31.45

J	K	L	M	N	P	S	wt
3.25	.10	.40	1.15	1.86	.64	.150	grams
82.55	2.54	10.16	29.21	47.24	16.26	3.81	74.0



electrical schematic



Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

REV. A
M107406
ZDC-10-1
WZ/TD/CP/AM
070228