


Engineering Development Model

Power Splitter/Combiner WP4-ED12616A/4_12

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DQ1225

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		2050		3000 MHz
Isolation	2050 - 3000 MHz		25	dB
Insertion Loss Above 6.0 dB	2050 - 3000 MHz		0.80	dB
Phase Unbalance	2050 - 3000 MHz		1.179	deg.
Amplitude Unbalance	2050 - 3000 MHz		0.160	dB
VSWR	SUM Port		1.40	(:1)
	OUT Ports		1.30	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-65°C to 150°C

PIN CONNECTIONS	
SUM PORT	2
PORT 1	12
PORT 2	10
PORT 3	6
PORT 4	4
GROUND	1,3,5,7,8,9,11,paddle

Functional Diagram

