

Power Splitter/Combiner

ZAPD-ED12417/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : F14

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		660		2400 MHz
Isolation	660 - 2400 MHz		20	dB
Insertion Loss Above 3.0 dB	660 - 2400 MHz		0.30	dB
Phase Unbalance	660 - 2400 MHz		0.211	deg.
Amplitude Unbalance	660 - 2400 MHz		0.082	dB
VSWR	SUM Port		1.30	(:1)
	OUT Ports		1.25	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Functional Diagram

