

Engineering Development Model

Power Splitter/Combiner

2 Way-0°

ZAPD-ED17175/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : F53

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		600		2400 MHz
Isolation	600-2400 MHz		23	dB
Insertion Loss Above 3.0 dB	600-2400 MHz		0.5	dB
Phase Unbalance	600-2400 MHz		1.0	deg.
Amplitude Unbalance	600-2400 MHz		0.1	dB
VSWR	SUM Port		1.4	(:1)
	OUT Ports		1.2	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1+V
PORT 2	2+V

Functional Diagram



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



REV. X1
ZAPD-ED17175/1
2/4/2015
Page 1 of 1