

Power Splitter/Combiner

ZAPD-ED9826/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : F14

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1400		4400 MHz
Isolation	1400 - 4400 MHz		29	dB
Insertion Loss Above 3.0 dB	1400 - 4400 MHz		0.51	dB
Phase Unbalance	1400 - 4400 MHz		0.328	deg.
Amplitude Unbalance	1400 - 4400 MHz		0.022	dB
VSWR	SUM Port		1.41	(:1)
	OUT Ports		1.21	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2

Functional Diagram

