30 dB DC Pass

High Power Bi-Directional Coupler ZGBDC30-372HP+

Up to 250W 380 to 3700 MHz 50Ω

The Big Deal

• High Power Handling: 250W

Low Insertion Loss: 0.20 dB typ.*



CASE STYLE: HT1760-1

Product Overview

The Mini-Circuits ZGBDC30-372HP+ broadband high power directional coupler offers excellent performance across a wide range of popular frequency bands. Built using low loss suspended substrate construction, the ZGBDC30-372HP+ can pass up to 3A of DC current from input to output and handle up to 250W CW. The rugged sealed construction makes this coupler ideal for use in field applications or remote monitoring sites; however, it is also ideal for high power lab testing.

Key Features

Feature	Advantages
Excellent Insertion Loss , 0.20 dB Typ*	With extremely low insertion loss, this coupler is ideal for critical high power applications.
Ultra High Return Loss, 22 dB Typ	Outstanding Return loss makes this coupler ideal for sensitive power measurement and other signal distribution applications.
High Power Handling, 250W	Up to 250W CW power handling, combined with low insertion loss and excellent VSWR support operation in high power applications such as transmitters, base stations and high power device characterization.
Wide bandwidth	Covering 380-3700 MHz, the ZGBDC30-372HP+ covers the most popular Cellular, PCS, DCS, WiMAX, and LTE bands.
Excellent Directivity and Coupling Flatness	Typical 20 dB directivity and ±0.4 dB of Coupling flatness provides accurate signal sampling of forward or reflected power.
Passes DC Current, 3A	Capable of passing 3A current, input to output; this coupler is suited for application using remote antenna control or other remote motorized requirements.

^{*}Does not include coupling loss

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

30 dB DC Pass

High Power Bi-Directional Coupler zgbdc30-372HP+

Up to 250W 50Ω 380 to 3700 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	3A

Permanent damage may occur if any of these limits are exceeded

Coaxial Connections

INPUT	IN
OUTPUT	OUT
COUPLED FORWARD	CPL IN
COUPLED REVERSE	CPL OUT

Outline Drawing



Outline Dimensions (inch)

	(IIIIII /					
G	F	E	D	С	В	Α
2.040	0.18	5.565	0.18	1.00	2.4	5.93
51.82	4.57	141.35	4.57	25.40	60.96	150.62
wt		M	L	K	J	Н
grams		1.09	1.09	0.99	0.50	0.200
700		27.60	27.60	25.15	12.70	5.08

Features

- wide frequency range, 380 3700 MHz
- good coupling flatness, ±0.4 dB typ. (600-3700 MHz)
- high directivity, 20 dB typ.
- very good return loss, 22 dB typ.
- high power, up to 250W
- · DC current pass through input to output

Applications

- PCN • cellular • GSM • lab use
- WiMAX • ISM



CASE STYLE: HT1760-1

Connectors	Model
N-Type	ZGBDC30-372HP+

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Liectrical Specifications at 25 C								
Parameter	Frequency (MHz)	Min.	Тур.	Max.	Units			
Operating Frequency		380		3700	MHz			
	380-600	_	31.5±2.0	_				
Coupling	600-2700	_	30.1±1.0	_	dB			
	2700-3700	_	30.9±1.2	_				
	380-600	_	±1.1	±2.0				
Coupling Flatness	600-2700	_	±0.4	±0.75	dB			
	2700-3700	_	±0.4	±0.9				
Mainline Loss¹	380-600	_	0.04	0.20				
	600-2700	_	0.09	0.30	dB			
	2700-3700	_	0.17	0.35				
Directivity	380-600	20	39	_				
	600-2700 15 32		_	dB				
	2700-3700	14	24	_				
	380-600	_	29	_				
Return Loss	600-2700	_	29	_	dB			
	2700-3700	_	25	_				
	380-600	_	_	250				
Input Power ²	600-2700	_	_	250	W			
	2700-3700	_	_	150				

^{1.} Does not include coupling loss

Electrical Schematic



ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.

^{2.} At 25°C with no DC current. Derate linearly to 100W (380-2700 MHz) and to 64W (2700-3600 MHz) from 25°C to 100°C. Output load VSWR 2.0:1 max.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Typical Performance Data

Frequency Mainline Los (MHz) (dB)		Coupling (dB)		Directivity (dB)		Return Loss (dB)			
, ,	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
50	0.01	48.54	49.05	24.54	24.61	52.9	52.0	45.4	45.5
380	0.03	32.82	32.81	35.88	45.58	32.6	32.3	33.3	32.7
600	0.04	30.56	30.59	35.87	49.06	29.7	29.3	32.7	32.9
1500	0.08	29.81	29.90	47.23	41.48	32.2	32.6	31.2	30.6
2000	0.10	30.08	30.24	22.93	29.24	34.8	40.2	22.7	23.9
2500	0.12	29.99	30.16	29.63	28.61	32.4	42.8	27.3	28.5
2700	0.13	30.31	30.52	23.98	25.02	45.1	36.3	23.9	24.1
3000	0.14	30.59	30.85	20.44	26.58	29.2	31.0	27.2	26.5
3600	0.17	31.06	31.34	22.29	20.98	34.5	33.9	23.9	23.7
3700	0.18	31.26	31.59	20.16	20.47	27.1	26.4	24.8	24.9
4000	0.23	32.35	32.62	19.59	20.48	19.9	20.7	22.0	22.3

^{*} Does not include coupling loss.







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp