# 35dB, DC Pass

# **High Power Bi-Directional Coupler**

ZGBDC35-93HP+

Up to 250W  $50\Omega$ 

900 to 9000 MHz

## **The Big Deal**

• High Power Handling: 250W Low Insertion Loss: 0.20 dB\* Rugged IP67 Weatherproof case



CASE STYLE: HT1762

## **Product Overview**

Mini-Circuits ZGBDC35-93HP+ broadband high power bi-directional coupler offers excellent performance across a wide range of popular frequency bands. Built using low loss airline construction, the ZGBDC35-93HP+ can pass up to 3A of DC current from input to output and handle up to 250W CW. Rugged sealed construction makes this coupler ideal for use in field applications or remote monitoring sites; however, it is also ideal for high power lab testing.

## **Key Features**

Feature	Advantages					
Excellent Insertion Loss , 0.20 dB Typ*	With extremely low insertion loss, this coupler is ideal for critical high power applications.					
Ultra High Return Loss, 26 dB Typ	Outstanding Return loss makes this coupler ideal for sensitive power measurement and other signal distribution applications.					
High Power Handling, 250W	Up to 250W CW power handling, combined with low insertion loss and excellent VSWR support operation in high power applications such as transmitters, base stations and high power device characterization.					
Wide bandwidth	900-9000 MHz coverage includes many popular cellular, WiMAX, LTE, ISM, satellite, P2P, aviation, maritime, defense, and radar bands					
Excellent Directivity and Coupling Flatness	Typical 25 dB directivity and ±0.8 dB of Coupling flatness provides accurate signal sampling of forward or reflected power.					
Passes DC Current, 3A	Capable of passing 3A current, input to output; this coupler is suited for application using remote antenna control or other remote motorized requirements.					
IP67 Weatherproof Case	With an Ingress Protection rating of IP67, the ZGBDC6-362HP+ is designed to operate in harsh outdoor applications.					

<sup>\*</sup>Does not include coupling loss

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

# 35dB DC Pass

# High Power Bi-Directional Coupler zgbdc35-93HP+

 $50\Omega$ **Up to 250W**  900 to 9000 MHz

#### **Maximum Ratings**


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	3A

Permanent damage may occur if any of these limits are exceeded

#### **Coaxial Connections**

INPUT	IN (N-TYPE)
OUTPUT	OUT (N-TYPE)
COUPLED IN	CPL IN (SMA)
COUPLED OUT	CPL OUT (SMA)

### **Outline Drawing**



## Outline Dimensions (inch)

G	F	Ε	D	С	В	Α
	.15	2.650	.60	.80	1.10	3.85
	3.81	67.31	15.24	20.32	27.94	97.79
wt		М	L	K	J	Н
grams		.60	.60	.50	.40	.150
200.0		15 24	15 24	12 70	10 16	3 81

#### **Features**

- wide frequency range, 900-9000 MHz
- good coupling flatness, ±0.8 dB typ.
- high directivity, 25 dB typ.
- good VSWR, 1.10:1 typ.
- high power, up to 250W
- DC current pass through input to output

## **Applications**

- cellular • PCN
- GSM • lab use
- WiMAX • ISM

CASE STYLE: HT1762

Connectors Model N-Type/SMA ZGBDC35-93HP+

#### +RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications at 25°C

Exercises of Exerc									
Parameter	Frequency (MHz)	Min.	Тур.	Max.	Units				
Operating Frequency		900		9000	MHz				
	900-1050	33	35.4	37.5					
Coupling	1050-8000	31	34.5	37.5	dB				
	8000-9000	31	34.3	37					
	900-1050	_	- ±0.5 1.2						
Coupling Flatness	1050-8000	_	±0.8	1.4	dB				
	8000-9000	_	±0.6	1.3					
Mainline Loss <sup>1</sup>	900	_	0.03	0.2					
	6000	_	0.10	0.25	dB				
	9000	_	0.18	0.3					
	900	22	26	_					
	3000	20	25	_					
Directivity	6000	14	19	_	dB				
	8000	12	16	_					
	9000	8	11	_					
Return Loss (Input)	900-6000	14	19	_	dB				
neturii Loss (iliput)	6000-9000	6000-9000 14 17		_	UD				
Return Loss (Output)	900-6000	14	19	_	dB				
neturn 2055 (Output)	6000-9000	14	18	_	UB				
Return Loss (Coupling)	900-6000	15	22	_	dB				
Return Loss (Coupling)	6000-9000	14	18	_	UD				
Input Power <sup>2</sup>	900-6000	_	_	250	W				

<sup>1.</sup> Does not include coupling loss.

#### **Electrical Schematic**



ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


<sup>2.</sup> At 25°C with no DC current. Derate linearly to 200W (900-9000 MHz) and to 100W (600-9000 MHz) from 25°C to 100°C. Output load VSWR 2.0:1 max.

## **Typical Performance Data**

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
. ,	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
500.00	0.01	40.05	40.08	28.50	31.18	56.18	45.81	25.02	25.47
1000.00	0.01	35.59	35.61	25.01	30.19	39.69	38.27	21.92	22.20
2000.00	0.02	35.22	35.28	23.57	28.02	30.95	30.91	26.19	24.46
4000.00	0.05	34.69	34.77	15.20	27.85	22.66	22.63	21.72	21.00
6000.00	0.07	34.11	34.20	22.89	27.93	20.88	20.93	19.81	19.18
8000.00	0.09	33.83	33.87	14.24	20.63	19.82	19.65	18.88	18.28
10000.00	0.19	33.72	33.85	27.60	13.53	15.85	15.92	20.95	21.44
11000.00	0.10	34.03	34.34	19.26	18.48	21.08	21.55	20.58	21.73
12000.00	0.09	34.00	34.05	18.41	15.08	27.23	27.24	23.65	24.25
12400.00	0.12	33.35	33.29	13.75	23.37	20.11	20.46	25.83	25.27







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp