

Engineering Development Model

Power Splitter/Combiner ZB4PD-ED5336A/1

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : UU188

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	4400		7500	MHz
Isolation		28		dB
Insertion Loss Above 6.0 dB		0.65		dB
Phase Unbalance		1.30		deg.
Amplitude Unbalance		0.15		dB
VSWR	SUM Port	1.15		(:1)
	OUT Ports	1.15		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Functional Diagram

