

Amplifier

ZHL-ED12129B/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : HM1099

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	50		550	MHz
Gain		49		dB
Output Power @1 dB compr.		40.00		dB
Noise Figure		7.0		dB
VSWR				
IN		1.37		(:1)
OUT		2.50		(:1)
DC Power				
Voltage		24.0		V
Current		4.4		A

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C