# Suspended Substrate Stripline Filters and Multiplexers

 $50\Omega$ DC to 40 GHz

## The Big Deal

- Low insertion loss
- Ultra-wide passband width
- Fast roll-off with wide stopband
- Good power handling and temperature stability
- Passband up to 40 GHz
- Stopband up to 40 GHz



### **Product Overview**

Mini-Circuits' Suspended Substrate Stripline filters offer low insertion loss by implementing printed circuit board suspended between two parallel ground planes, providing high Q. Low insertion loss combined with wide stopband makes them an excellent choice for wideband instruments and systems like ECM, ECCM, ELINT and ultrabroadband receivers.

Low pass, high pass, band pass, band stop, diplexer and multiplexer designs can be realized with this technology. Advanced filter design and construction can achieve stopband width greater than 6x the center frequency, and temperature stability will be better than other printed circuit realizations because the fields are mainly in the air rather than in a dielectric. The inside walls of the housing hold the circuit and prevent movement that could be caused by vibration or mechanical shock, making these designs excellent candidates for harsh operating environments.

Suspended substrate stripline filters can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## **Key Features**

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitters
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide, spur-free stop band results in better receiver sensitivity
High power handling	Well suited for transmitter applications
Excellent temperature stability	Ensures minimal variation in electrical performance across temperature

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited arranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **High Pass Filter**

50Ω 11000 to 40000 MHz

## ZHSS-K11G+



Generic photo used for illustration purposes only

CASE STYLE: UJ2936

Connectors	Model
2 92mm-F	7HSS-K11G+

#### Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC - 6500	60	80	-	dB
		F1-F2	6500 - 8500	20	40	-	dB
Pass Band	Insertion Loss	F3-F4	11000 - 40000	-	1.5	2.5	dB
	VSWR	F3-F4	11000 - 40000	-	2	-	:1

Maximum Ratings			
Operating Temperature	-40°C to 85°C		
Storage Temperature	-55°C to 100°C		
RF Power Input	2 W @ 25°C		

Permanent damage may occur if any of these limits are exceeded.

## **Applications**

**Features** 


- 5G
- · Very wideband test and instrumentation

· Wider passband up to 40000 MHz


Low insertion loss of 1 dB typical
Sharp rejection of 90 dB typical
Connectorized package

- Satellite communication
- Transmitter / Receiver

#### **Functional Schematic**




#### **Typical Frequency Response**





+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


#### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (ns)		
10	121.58	623.54	11000	0.39		
100	123.02	12063.74	12500	0.27		
1000	109.06	552.19	14000	0.23		
2000	128.96	215.32	15500	0.19		
3000	100.69	112.37	17000	0.18		
4000	93.02	62.29	18500	0.17		
5200	95.59	41.03	20000	0.16		
6500	94.04	29.75	21500	0.15		
8500	44.63	20.01	23000	0.15		
9000	31.36	18.64	24500	0.15		
9400	20.33	16.05	26000	0.15		
10000	3.62	3.05	27500	0.14		
11000	1.03	1.20	29000	0.14		
15000	0.83	1.52	30500	0.14		
20000	0.66	1.34	32000	0.14		
20200	0.67	1.34	33500	0.14		
30000	0.65	1.31	35000	0.14		
31000	0.62	1.19	36500	0.14		
35000	0.68	1.15	38000	0.14		
40000	0.86	1.37	40000	0.14		









#### Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.


C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


#### **Coaxial Connections**

PORT - 1	2.92mm-Female		
PORT - 2	2.92mm-Female		

#### **Outline Drawing**







#### Outline Dimensions (inch )

Α	В	С	D	E	F
.43	.60	.48	1.30	.440	.08
10.9	15.2	12.1	33.0	11.18	2.0
G . <b>22</b> 5.5	H <b>.070</b> 1.78	J . <b>30</b> 7.6	K . <b>25</b> 6.4		Wt. grams <b>21</b>

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp