DC Pass, High Power

Power Splitter/Combiner zc16PD-02183-S+

16 Way-0° 50Ω 2000 to 18000 MHz

The Big Deal

- Super wideband, 2 to 18 GHz
- Low insertion loss, 2.3 dB typ. at 10 GHz
- High Isolation, 33 dB typ. at 10 GHz
- 20W power handling
- Low amplitude unbalance, 0.12 dB typ. at 10 GHz



CASE STYLE: UU179-1

Product Overview

Mini-Circuits' ZC16PD-02183-S+ is a super wideband 16-way 0° splitter/combiner providing coverage from 2 to 18 GHz, supporting a wide range of applications including S-Band, C-Band, X-Band, Ku-Band and instrumentation and many more. This model provides 20W power handling as a splitter and very low insertion loss across the entire operating frequency range, minimizing power dissipation and delivering excellent signal power transmission from input to output. The ZC16PD-02183-S+ comes housed in a case measuring 8.27 x 3.62 x 0.5" with SMA connectors.

Key Features

Feature	Advantages		
Super wideband, 2 to 18 GHz	Extremely wide frequency range supports many broadband applications in a single model.		
Low insertion loss, 2.3 dB typ. at 10 GHz	The combination of 20W power handling and low insertion loss makes this model a suitable candidate for distributing signals while maintaining excellent transmission of signal power.		
High isolation, 33 dB typ. at 10 GHz	Minimizes interference between ports.		
High power handling: • 20W as a splitter at 25°C • 1.6W as a combiner	The ZC16PD-02183-S+ is suitable for systems with a wide range of power requirements.		
Low amplitude unbalance, 0.12 dB at 10 GHz	Produces nearly equal output signals, ideal for parallel path and multichannel systems.		
DC Passing, 510mA input to output	Supports applications where DC power is needed through the RF line.		

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp

DC Pass, High Power

Power Splitter/Combiner

ZC16PD-02183-S+

16 Way-0° 50Ω 2000 to 18000 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	20W* max.
Internal Dissipation	1.6W max.
DC Current	510 mA


Permanent damage may occur if any of these limits are exceeded. * Derate linearly to13W at 100°C

Coaxial Connections

Sum Port	S
Port 1-16	1-16

Outline Drawing





Weight: 750 grams; Dimensions are in inches (mm). Tolerances: 2 Pl.±.03; 3 Pl. ± .015

Electrical Schematic



Features

- Super wideband, 2000 18000 MHz
- Low insertion loss, 2.3 dB typ at 10 GHz
- Low amplitude unbalance, 0.12 dB typ at 10 GHz
- Excellent VSWR, 1.19:1 typ at 10 GHz
- High isolation, 33 dB typ at 10 GHz

Applications

- Fixed satellite
- Mobile
- Space research



Generic photo used for illustration purposes only CASE STYLE: UU179-1

Connectors Model

SMA-Fem ZC16PD-02183-S+

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C


Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit	
Frequency Range		2000		18000	MHz	
In a self-out I also Albassa 40 O dD	2000-8000		1.4	3.0	dB	
Insertion Loss Above 12.0 dB	8000-18000		2.9	5.6		
Indiation	2000-8000	16	27		dB	
Isolation	8000-18000	18	33			
Dhara Habalana (M	2000-8000		1.7	6	Degree	
Phase Unbalance (±) ¹	8000-18000		4.5	9		
Amplitude Unbalance (±)1	2000-8000		0.10	0.5	4D	
	8000-18000		0.16	0.6	dB	
VSWR (Port S)	2000-8000		1.11	1.5	:1	
	8000-18000		1.13	1.6		
VSWP (Port 1 16)	2000-8000		1.11	1.6	.1	
VSWR (Port 1-16)	8000-18000		1.08	1.6	:1	


^{1.} With reference to average


Typical Performance Data

Freq. (MHz)	Total Loss¹ (dB)	Amplitude Unbalance (dB)	Isolation (dB)		Phase Unbalance (deg.)	VSWR S	VSWR 1
	S-1		1-2	14-15			
2000	12.78	0.08	32.88	38.22	0.56	1.08	1.06
3000	13.00	0.08	32.03	32.06	0.70	1.06	1.16
4000	13.23	0.08	28.31	37.58	0.95	1.20	1.09
5000	13.40	0.09	26.87	29.97	1.57	1.12	1.11
6000	13.56	0.06	25.45	32.60	1.97	1.04	1.17
7000	13.75	0.09	25.43	36.75	2.06	1.05	1.06
8000	14.01	0.10	28.36	33.60	2.22	1.28	1.04
10000	14.30	0.12	33.45	33.77	3.14	1.19	1.06
12000	14.64	0.13	26.88	36.83	3.82	1.12	1.04
14000	14.95	0.16	37.27	48.34	4.49	1.06	1.10
16000	15.35	0.14	30.51	42.70	5.36	1.20	1.08
18000	15.72	0.24	24.06	39.12	5.90	1.27	1.05

^{1.} Total Loss = Insertion Loss +12dB splitter loss.







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp