Low Noise Amplifier

50**Ω** 0.4 to 3.0 GHz

ZKL-33ULN-S+

The Big Deal

- Ultra Low Noise Figure, 0.36 dB typ. at 0.9 GHz
- High Dynamic Range
- Small connectorized package

CASE STYLE: BY493

Product Overview

The ZKL-33ULN-S+ (RoHS compliant) uses Mini-Circuits' E-PHEMT technology to offer very high gain with a combination of ultra low noise figure over a broad frequency range and high OIP3. Housed in a rugged shielded package with class 3A ESD rating and internal voltage regulator, this amplifier supports a wide variety of applications requiring moderate power output, low distortion and 50 ohm matched input/output ports.

Key Features

| Feature | Advantages | | | | | | |
|---|--|--|--|--|--|--|--|
| Ultra Low Noise Figure, 0.36 dB at 0.9 GHz | Outstanding world class noise figure performance. | | | | | | |
| High OIP3 vs. DC power con- sumption +36 dBm typical at 0.9 GHz | Combination of Low Noise and High OIP3 make this model ideal for use in a Low Noise Receiver Front End (RFE) | | | | | | |
| Small Size, 1.38" x 1.5" | The small size and construction enable the ZKL-33ULN-S+ to be used in extremely compact connector- ized applications. | | | | | | |

Coaxial <u>.ow Noise Amplifier</u>

0.4 to 3.0 GHz 50**Ω**

Features

- Low Noise Figure, 0.36 dB typ. at 0.9 GHz
- High OIP3, +36 dBm at 0.9 GHz typ.
- High Pout, P1dB, +18 dBm typ. at 0.9 GHz typ.
 High Gain, 35.0 dB at 0.9 GHz typ.

Applications

- Base station infrastructure
- Portable Wireless
- LTE
- GPS • GSM
- Airborne radar



Electrical Specifications at 25°C and 5.0 V unless noted

| Parameter | Condition (GHz) | Min. | Тур. | Max. | Units |
|-------------------------------------|-----------------|------|------|------|-------|
| Frequency Range | | 0.4 | | 3.0 | GHz |
| | 0.4 | | 0.29 | | |
| | 0.9 | | 0.36 | 0.70 | |
| Noise Figure | 1.5 | | 0.50 | | dB |
| | 2.0 | | 0.68 | | |
| | 3.0 | | 1.44 | | |
| | 0.4 | | 47 | | |
| | 0.9 | 33 | 35 | 37 | |
| Gain | 1.5 | | 27 | | dB |
| | 2.0 | | 22 | | |
| | 3.0 | | 15 | | |
| | 0.4 | | 18.0 | | |
| | 0.9 | | 18.0 | | |
| Output Power @ 1 dB compression | 1.5 | 17 | 18.0 | | dBm |
| | 2.0 | | 18.0 | | |
| | 3.0 | | 13.5 | | |
| | 0.4 | | 34 | | |
| | 0.9 | 34 | 36 | | |
| Output IP3 | 1.5 | | 37 | | dBm |
| | 2.0 | | 38 | | |
| | 3.0 | | 36 | | |
| | 0.4 | | 1.28 | | |
| | 0.9 | | 1.25 | | |
| Input VSWR | 1.5 | | 1.41 | | :1 |
| | 2.0 | | 1.33 | | |
| | 3.0 | | 1.34 | | |
| | 0.4 | | 1.65 | | |
| | 0.9 | | 1.29 | | |
| Output VSWR | 1.5 | | 1.12 | | :1 |
| | 2.0 | | 1.05 | | |
| | 3.0 | | 1.25 | | |
| Active Directivity (Isolation-Gain) | 0.4-3.0 | | 8 | | dB |
| DC Supply Voltage | | — | 5.0 | — | V |
| Supply Current | | _ | 100 | 150 | mA |



ZKL-33ULN-S+

Generic photo used for illustration purposes only CASE STYLE: BY493 Connectors Model ZKL-33ULN-S+ SMA

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


ZKL-33ULN-S+

50**Ω** 0.4 to 3.0 GHz


Maximum Ratings

| Parameter | Ratings | | | | | |
|----------------------------|---|--|--|--|--|--|
| Operating Temperature | -40°C to 85°C Case | | | | | |
| Storage Temperature | -55°C to 100°C | | | | | |
| DC Voltage | 5.5 V | | | | | |
| Input RF Power (no damage) | From 400 MHz to 1500 MHz: -10 dBm to 0 dBm From 1500 MHz to 3000 MHz: 0 dBm to +10 dBm | | | | | |
| Power Consumption | 0.75 W | | | | | |

Permanent damage may occur if any of these limits are exceeded.



Outline Drawing



Â

NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminal. See Application Note. <u>AN-40-010</u>.

Outline Dimensions (inch)


| wt | R | Q | Р | Ν | М | L | к | J | н | G | F | Е | D | С | В | А |
|-------|------|------|------|-------|-------|-------|------|-------|-------|------|-------|------|------|-------|-------|-------|
| grams | .35 | .11 | .19 | 1.000 | 1.281 | 1.50 | .125 | .66 | .76 | .27 | .52 | .35 | .125 | .75 | 1.00 | 1.38 |
| 40 | 8.89 | 2.79 | 4.83 | 25.40 | 32.54 | 38.10 | 3.18 | 16.76 | 19.30 | 6.86 | 13.21 | 8.89 | 3.18 | 19.05 | 25.40 | 35.05 |

Typical Performance Data/Curves

ZKL-33ULN-S+

50**Ω** 0.4 to 3.0 GHz

| FREQUENCY (MHz) | GAIN (dB) | DIRECTIVITY (dB) | VSWR (:1) | | POUT at 1dB COMPR. (dBm) | NOISE FIGURE (dB) | OUTPUT IP3 (dBm) |
|--------------------|--------------|---------------------|--------------|------|-----------------------------------|-------------------------|------------------------|
| | | | IN | OUT | | | |
| 400 | 47.4 | 6.7 | 1.28 | 1.65 | 18.5 | 0.3 | 33.9 |
| 500 | 44.4 | 6.8 | 1.19 | 1.54 | 18.6 | 0.3 | 34.1 |
| 600 | 41.6 | 7.0 | 1.17 | 1.46 | 18.7 | 0.3 | 34.7 |
| 900 | 35.2 | 7.3 | 1.25 | 1.29 | 18.3 | 0.4 | 36.0 |
| 1100 | 31.9 | 7.7 | 1.33 | 1.23 | 17.9 | 0.5 | 36.2 |
| 1500 | 26.8 | 7.8 | 1.41 | 1.12 | 17.9 | 0.5 | 36.8 |
| 1700 | 24.6 | 8.3 | 1.38 | 1.08 | 17.6 | 0.6 | 38.5 |
| 2000 | 22.1 | 8.1 | 1.35 | 1.05 | 18.0 | 0.7 | 37.6 |
| 2500 | 18.3 | 9.1 | 1.29 | 1.17 | 16.2 | 0.9 | 38.4 |
| 3000 | 15.0 | 10.5 | 1.34 | 1.25 | 13.4 | 1.4 | 36.1 |



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

