

DC Pass, High Power

Power Splitter/Combiner

ZC4PD-5R263-S+

4 Way-0° 50Ω 500 to 26500 MHz

The Big Deal

- Super wideband, 0.5 to 26.5 GHz
- Low insertion loss, 2.7 dB typ.
- High Isolation, 34 dB typ.
- 20W power handling
- Low amplitude unbalance, 0.15 dB typ.



CASE STYLE: UU2413-1

Product Overview

Mini-Circuits' ZC4PD-5R263-S+ is a super wideband 4-way 0° splitter/combiner providing coverage from 0.5 to 26.5 GHz, supporting a wide range of applications including 5G, Ku-Band, K-Band, instrumentation and many more. This model provides 20W power handling as a splitter and very low insertion loss across the entire operating frequency range, minimizing power dissipation and delivering excellent signal power transmission from input to output. The ZC4PD-5R263-S+ comes housed in a case measuring 6.24 x 2.03 x 0.5".

Key Features

Feature	Advantages
Ultra-wideband, 0.5 to 26.5 GHz	Extremely wide frequency range supports many broadband applications in a single model.
Low insertion loss, 2.7 dB typ. at 18 GHz	The combination of 20W power handling and low insertion loss makes this model a suitable candidate for distributing signals while maintaining excellent transmission of signal power.
High isolation, 34 dB typ. at 18 GHz	Minimizes interference between ports.
High power handling: <ul style="list-style-type: none">• 20W as a splitter at 25°C• 2W as a combiner	The ZC4PD-5R263-S+ is suitable for systems with a wide range of power requirements.
Low amplitude unbalance, 0.15 dB at 18 GHz	Produces nearly equal output signals, ideal for parallel path and multichannel systems.
DC Passing, 530mA	Supports applications where DC power is needed through the RF line.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



DC Pass, High Power Power Splitter/Combiner

ZC4PD-5R263-S+

4 Way-0° 50Ω 500 to 26500 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	20W* max.
Internal Dissipation	2W max.
DC Pass	530mA

Permanent damage may occur if any of these limits are exceeded.
*Derates linearly to 14W at 100°C

Coaxial Connections

Sum Port	S
Port 1	1
Port 2	2
Port 3	3
Port 4	4

Outline Drawing



Features

- Super wideband, 500 to 26500 MHz
- Low insertion loss, 2.7 dB typ.
- Low amplitude unbalance, 0.15 dB typ.
- Excellent VSWR, 1.17:1 typ.
- High isolation, 34 dB typ.

Applications

- 5G
- Fixed satellite
- Space research
- Mobile



Generic photo used for illustration purposes only

CASE STYLE: UU2413-1

Connectors	Model
SMA-Fem	ZC4PD-5R263-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		500		26500	MHz
Insertion Loss Above 6.0 dB	500-8000		1.3	2.4	dB
	8000-18000		2.7	4	
	18000-26500		4.1	5.2	
Isolation	500-8000	15	31	—	dB
	8000-18000	18	34	—	
	18000-26500	18	35	—	
Phase Unbalance (±) ¹	500-8000		0.8	4	Degree
	8000-18000		1.6	5	
	18000-26500		3.1	6	
Amplitude Unbalance (±) ¹	500-8000		0.11	0.4	dB
	8000-18000		0.15	0.4	
	18000-26500		0.22	0.4	
VSWR (Port S)	500-8000		1.13	1.6	:1
	8000-18000		1.17	1.5	
	18000-26500		1.17	1.6	
VSWR (Port 1-4)	500-8000		1.11	1.4	:1
	8000-18000		1.15	1.5	
	18000-26500		1.22	1.6	





1. With reference to average

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)				Amp. Unb. (dB)	Isolation (dB)			Phase Unb. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	1-4	3-4						
500	6.33	6.34	6.32	6.33	0.01	17.46	24.14	17.23	0.18	1.04	1.05	1.05	1.04	1.04
2000	6.76	6.78	6.78	6.79	0.03	43.73	35.64	50.79	0.28	1.18	1.22	1.22	1.23	1.24
4000	7.15	7.18	7.18	7.20	0.05	27.10	34.95	28.68	0.46	1.12	1.08	1.07	1.09	1.09
6000	7.48	7.51	7.52	7.56	0.08	34.19	37.11	34.22	0.57	1.06	1.01	1.01	1.00	1.01
8000	7.81	7.84	7.86	7.92	0.10	36.29	44.01	40.23	0.64	1.10	1.08	1.09	1.09	1.09
10000	8.12	8.14	8.17	8.24	0.12	39.35	50.93	40.65	0.69	1.07	1.03	1.04	1.02	1.01
12000	8.42	8.45	8.48	8.57	0.15	39.26	46.02	40.04	0.68	1.04	1.13	1.10	1.13	1.15
13000	8.62	8.64	8.68	8.77	0.15	37.75	66.91	38.78	0.72	1.18	1.22	1.21	1.19	1.22
14000	8.72	8.74	8.80	8.88	0.16	47.27	49.47	41.67	0.64	1.03	1.13	1.09	1.13	1.13
15000	8.93	8.95	9.00	9.10	0.17	31.21	45.48	31.05	0.60	1.25	1.18	1.17	1.17	1.18
16000	9.01	9.05	9.12	9.20	0.19	31.56	50.61	30.83	0.76	1.15	1.07	1.05	1.05	1.07
18000	9.36	9.40	9.47	9.55	0.19	33.50	42.29	35.63	0.66	1.27	1.16	1.16	1.15	1.16
20000	9.71	9.75	9.83	9.93	0.22	29.71	42.54	30.72	0.64	1.35	1.26	1.27	1.27	1.29
22000	9.97	10.04	10.09	10.21	0.24	29.51	46.82	31.14	0.64	1.29	1.24	1.28	1.27	1.28
26500	10.52	10.60	10.64	10.80	0.28	38.76	47.93	39.93	0.89	1.05	1.12	1.08	1.10	1.11

1. Total Loss = Insertion Loss + 6dB splitter theoretical loss.

Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 35166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
ECO-025212
ZC4PD-5R263-S+
MCL NY
250502
Page 2 of 2