Power Splitter/Combiner zn2PD-9G-S+

2 Way-0° 50Ω 30W 1700 to 9000 MHz

The Big Deal

- Wideband, 1700 to 9000 MHz
- High power, up to 30W as a splitter
- Low insertion loss, 0.5 dB
- Low unbalance, 0.1 dB, 1°
- High isolation, 22 dB



CASE STYLE: VVV180

Product Overview

Mini-Circuits' ZN2PD-9G-S+ is a 2-way 0° high-power splitter/combiner providing up to 30W power handling as a splitter (0.8W as a combiner) and low insertion loss across the 1700 to 9000 MHz frequency range. Its outstanding combination of high power handling and low loss minimize power dissipation and provide excellent signal power transmission from input to output. The ZN2PD-9G-S+ comes housed in a rugged aluminum alloy case measuring 1.8 x 1.75 x 0.65" with SMA connectors.

Key Features

| Feature | Advantages | | | | |
|--------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
| Wideband, 1700 to 9000 MHz | This model supports bandwidth requirements for a wide variety of applications. | | | | |
| High power handling: • 30W to 5800 MHz • 20W to 9000 MHz | The ZN2PD-9G-S+ is suitable for systems with a wide range of power requirements. | | | | |
| Low insertion loss, 0.5 dB | The combination of 30W power handling and low insertion loss makes this model a suitable candidate for distributing signals while maintaining excellent transmission of signal power. | | | | |
| Low unbalance: • 0.1 dB amplitude unbalance • 1° phase unbalance | Produces nearly equal output signals, ideal for parallel path and multichannel systems. | | | | |
| High isolation, 22 dB | Minimizes interference between ports. | | | | |
| DC Passing, 400mA (200mA each port) | Supports applications where DC power is needed through the RF line. | | | | |

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchaspers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/WCLStore/terms.jsp

Power Splitter/Combiner

ZN2PD-9G-S+

Generic photo used for illustration purposes only

CASE STYLE: VVV180

Model

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

ZN2PD-9G-S+

Connectors

SMA

2 Way-0° 30W 1700 to 9000 MHz 50Ω


Maximum Ratings

Operating Temperature (@<30W) -55°C to 60°C Operating Temperature (@<10W) -55°C to 100°C DC Current 400 mA (200mA for each port) Permanent damage may occur if any of these limits are exceeded

Coaxial Connections

| SUMPORT | S |
|---------|---|
| PORT 1 | 1 |
| PORT 2 | 2 |


Outline Drawing




Outline Dimensions (inch)

| G | F | E | D | С | В | Α |
|-------|------|-------|-------|-------|-------|-------|
| .125 | .125 | 1.675 | .125 | .66 | 1.75 | 1.80 |
| 3.18 | 3.18 | 42.55 | 3.18 | 16.76 | 44.45 | 45.72 |
| | | | | | | |
| wt | | M | L | K | J | Н |
| grams | | .88 | 1.13 | .63 | .31 | 1.625 |
| 65.2 | | 22 35 | 28 70 | 16 00 | 7 87 | 41 28 |

Electrical Schematic





Features

- very wideband, 1700 to 9000 MHz
- low insertion loss, 0.5 dB typ.
- good isolation, 22 dB typ.
- up to 30W power input as splitter
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 1 deg. typ.
- rugged shielded case

Applications

- UHF/VHF
- PCS/DCS
- defense & federal communications
- wireless

Flectrical Specifications at 25°C


| Liectifical Specifications at 25 C | | | | | | | |
|------------------------------------|--------------------------|------------------------|----------|----------|------|--------|--|
| Parameter | | Frequency (MHz) | Min. | Тур. | Max. | Unit | |
| Frequency Range | | | 1700 | | 9000 | MHz | |
| Insertion Loss | | 1700-6800 | _ | 0.5 | 1.2 | dB | |
| (above theoretical | 3 dB) | 6800-9000 | _ | 1.0 | 1.4 | | |
| Isolation | | 1700-6800 6800-9000 | 15 17 | 19 22 | | dB | |
| Phase Unbalance | | 1700-6800 | _ | 1.0 | 3.5 | Degree | |
| | | 6800-9000 | _ | 2.0 | 4.0 | | |
| Amplitude Unbalance | | 1700-6800 | _ | 0.15 | 0.4 | dB | |
| | | 6800-9000 | _ | 0.2 | 0.6 | | |
| VSWR (Port S) | | 1700-6800 | _ | 1.5 | | dB | |
| | | 6800-9000 | _ | 1.7 | | | |
| VSWR Output (Port 1-2) | | 1700-6800 | _ | 1.4 | | dB | |
| | | 6800-9000 | _ | 1.6 | | | |
| Power Handling ³ | As Splitter ¹ | 1700-6800 | _ | | 30 | Watt | |
| | As Combiner ² | 6800-9000 1700-9000 | _ | | 0.8 | | |


- All outputs must terminate 50 ohm (VSWR 1.5:1 or better)
- 2. As a combiner of non-coherent signals, max. power per port is 0.8 watt power rating divided by number of ports.
- 3. Alternative heat sinking and heat removal must be provided by the user to limit maximum base-plate temperature to 60°C, in order to ensure proper performance. For reference, this requires thermal resistance of user's external heat sink to be 10°C/W.

Typical Performance Data

| Frequency (MHz) | Total (d | Loss¹ B) | Amplitude Unbalance (dB) | Isolation (dB) | Phase Unbalance (deg.) | VSWR S | VSWR 1 | VSWR 2 |
|--------------------|-------------|-------------|--------------------------------|-------------------|------------------------------|-----------|-----------|-----------|
| | S-1 | S-2 | ` , | | , | | | |
| 1700.00 | 3.42 | 3.41 | 0.01 | 17.93 | 0.12 | 1.47 | 1.11 | 1.11 |
| 2200.00 | 3.31 | 3.33 | 0.02 | 27.76 | 0.12 | 1.15 | 1.06 | 1.06 |
| 2700.00 | 3.42 | 3.41 | 0.01 | 24.71 | 0.27 | 1.20 | 1.15 | 1.14 |
| 3700.00 | 3.70 | 3.70 | 0.00 | 20.67 | 0.32 | 1.66 | 1.42 | 1.41 |
| 4200.00 | 3.69 | 3.68 | 0.01 | 23.57 | 0.43 | 1.60 | 1.40 | 1.40 |
| 4700.00 | 3.57 | 3.54 | 0.03 | 29.47 | 0.39 | 1.38 | 1.30 | 1.32 |
| 5200.00 | 3.52 | 3.51 | 0.01 | 46.41 | 0.43 | 1.23 | 1.20 | 1.22 |
| 5700.00 | 3.57 | 3.57 | 0.00 | 28.00 | 0.49 | 1.17 | 1.12 | 1.15 |
| 6200.00 | 3.63 | 3.62 | 0.01 | 23.68 | 0.52 | 1.21 | 1.13 | 1.15 |
| 6700.00 | 3.62 | 3.64 | 0.02 | 24.46 | 0.28 | 1.28 | 1.12 | 1.12 |
| 7200.00 | 3.61 | 3.62 | 0.01 | 23.63 | 0.44 | 1.26 | 1.18 | 1.16 |
| 7700.00 | 3.70 | 3.65 | 0.05 | 28.05 | 0.68 | 1.24 | 1.18 | 1.11 |
| 8200.00 | 3.79 | 3.76 | 0.03 | 25.09 | 0.72 | 1.27 | 1.27 | 1.19 |
| 8700.00 | 3.87 | 3.81 | 0.06 | 28.49 | 1.10 | 1.30 | 1.42 | 1.33 |
| 9000.00 | 3.86 | 3.88 | 0.03 | 28.80 | 0.94 | 1.30 | 1.45 | 1.41 |

1. Total Loss = Insertion Loss + 3dB splitter loss





- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchaspers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/WCLStore/terms.jsp