

Power Splitter/Combiner 3 Way-0°

ZN3PD-ED14660/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : UU181

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	1800		6200	MHz
Isolation 1800-6200 MHz		23		dB
Insertion Loss Above 4.8 dB 1800-6200 MHz		0.90		dB
Phase Unbalance 1800-6200 MHz		3.00		deg.
Amplitude Unbalance 1800-6200 MHz		0.60		dB
VSWR	SUM Port	1.30		(:1)
	OUT Ports	1.30		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3

Functional Diagram

