

Power Splitter/Combiner

ZN4PD-ED14603

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : UU182

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	1600		6400	MHz
Isolation 1600-6400 MHz		24		dB
Insertion Loss Above 6.0 dB 1600-6400 MHz		0.90		dB
Phase Unbalance 1600-6400 MHz		3.00		deg.
Amplitude Unbalance 1600-6400 MHz		0.20		dB
VSWR	SUM Port	1.15		(:1)
	OUT Ports	1.15		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Functional Diagram

