

## Power Splitter/Combiner

8 Way-0°

**ZN8PD-ED14937**

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



**CASE STYLE : UU1676**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	2000		11000	MHz
Isolation		22		dB
Insertion Loss Above 9.0 dB		1.3		dB
Phase Unbalance		6.0		deg.
Amplitude Unbalance		0.4		dB
VSWR		1.30		(:1)
SUM Port				
OUT Ports		1.33		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
PORT 5	5
PORT 6	6
PORT 7	7
PORT 8	8

### electrical schematic

