

Coaxial Directional Coupler

ZDC-20-1+

50Ω

25 to 400 MHz



Generic photo used for illustration purposes only

CASE STYLE: M22

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	3
OUTPUT	2
COUPLED	1

Features

- excellent directivity, 35 dB typ.
- excellent mainline loss, 0.3 dB typ.
- high input power, up to 5W max.
- rugged shielded case

Applications

- VHF/HF
- instrumentation
- communication receivers & transmitters
- amateur radio

Connectors	Model
BNC	ZDC-20-1+
BRACKET (OPTION "B")	
BRACKET (OPTION "BR")	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Directional Coupler Electrical Specifications

FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT (W)		
	Nom.	Flatness	L		M		U		L		M		U			Typ.	L	MU
			Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.				
25-400	20±0.5	±0.5	0.2	0.25	0.3	0.35	0.35	0.5	25	20	35	25	25	20	1.25	3.0	5.0	

L = 25-50 MHz M = 50-300 MHz U = 300-400 MHz

1. Mainline loss includes theoretical power loss at coupled port.

Outline Drawing






Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
2.25	1.38	1.24	.50	.150	3.100	.138	1.238
57.15	35.05	31.50	12.70	3.81	78.74	3.51	31.45


J	K	L	M	N	P	S	wt
3.25	.10	.40	1.15	1.86	.64	.150	grams
82.55	2.54	10.16	29.21	47.24	16.26	3.81	74.0

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		Cpl
				In	Out	
25.00	0.13	19.97	35.76	34.28	33.88	39.90
45.00	0.14	19.98	35.38	33.99	31.38	38.66
80.00	0.14	19.98	34.30	33.78	27.78	36.78
120.00	0.14	20.01	33.33	34.16	24.90	35.11
160.00	0.14	20.02	32.39	33.90	22.55	33.12
210.00	0.15	20.08	30.90	34.23	20.48	31.35
260.00	0.15	20.13	29.21	33.58	18.79	29.50
310.00	0.10	20.15	27.48	32.70	17.46	28.08
360.00	0.15	20.23	25.48	31.39	16.45	26.85
400.00	0.21	20.28	24.37	29.89	15.74	26.00



Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/WCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
M151107
ZDC-20-1+
WZ/TD/CP
200608
Page 1 of 1