

50Ω DC-6 GHz



## Overview



Mini-Circuits panel-mounted structures provide clean, organized management of cable runs and connections in complex, high-volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.

## Mechanical Configuration

Parameter	Details
Configuration	24 x connector adapters: N-type female to N-type female
Mounting Bracket	Extended mounting brackets
Dimensions	19" width, 4U height

## Electrical Specifications at 25°C, per Adapter

FREQUENCY (GHz)	INSERTION LOSS (dB)		VSWR (:1) Max.		
	Typ.	Max.	DC-2 GHz	DC-4 GHz	DC-6 GHz
$f_L$ - $f_U$ DC-6	0.05	0.10	1.10	1.20	1.20



Please contact [testsolutions@minicircuits.com](mailto:testsolutions@minicircuits.com) for support