

4 x 4-Way Splitter/Combiner Panel **ZT-257**

50Ω 0.5 to 6 GHz SMA Female

THE BIG DEAL

- 4 x 4-way passive splitter / combiners
- Convenient panel-mounted design
- Wide bandwidth
- High power handling

Constraint Constraint

Generic photo used for illustration purposes only

Model No.	ZT-257
Case Style	YN2570
Connectors	SMA Female

RoHS Compliant
See our website for RoHS Compliance methodologies and qualifications

APPLICATIONS

- Production test setups
- Satcom signal distribution
- Cellular test applications

PRODUCT OVERVIEW

Mini-Circuits panel-mounted structures provide clean, organized management of cable runs and connections in complex, high-volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.

ZT-257 is a 1U height, rack-mountable panel incorporating 4 passive, wideband, 4-way splitter/combiners. All RF ports are SMA Female and accessible on the front panel.

ELECTRICAL SPECIFICATIONS

Pai	rameter	Frequency (MHz)	Min.	Тур.	Max.	Unit	
Frequency	Frequency		500		6000	MHz	
Insertion Loss		500-3000	_	0.4	0.9	dB	
(above theoretical 6	0 dB)	3000-6000	_	0.6	1.3	αв	
Isolation	500-600 16 19 —		dB				
isolation		600-6000	18	23	_	ав	
Phase Unbalance		500-6000	_	2	6	Degree	
Amplitude Unbaland	e	500-6000	_	0.15	0.4	dB	
\/C\\/D (Dovt C)	/R (Port S) 500-600 — 600-6000 —		_	1.3	1.5	:1	
VSVVR (POILS)			_	1.25	1.5		
VSWR (Port 1-4)		500-6000	_	1.15	1.25	:1	
Danner Handling	As Splitter ¹	s Splitter ¹ 500-6000 – 30		W			
Power Handling	As Combiner ²	500-6000	_	_	0.5	v V	

^{1.} All outputs must terminate 50 ohm (VSWR 1.2:1 or better)

^{2.} As a combiner of non-coherent signals, max. power is 0.5Watt per port.



4 x 4-Way Splitter/Combiner Panel **ZT-257**

50Ω 0.5 to 6 GHz SMA Female

MECHANICAL & ENVIRONMENTAL SPECIFICATIONS

Dimensions	19" (W) x 1U (H)						
Case Style	YN2570						
Case Material	Aluminum (with protective coating to prevent corrosion)						
RF Connectors	Panel	Connector	Quantity	Port Labels			
AF Connectors	Front	SMA female	20	S & 1-4 per splitter			
	Front Panel	Rear Panel					
Panel Marking	• ZT-257	• CE / EAC / UKCA • Serial number / date code / model name					
Panel Items	• Carry handles						
Temperature	Operating: 0 to +50 °C						

FUNCTIONAL SCHEMATIC (PER SPLITTER)








4 x 4-Way Splitter/Combiner Panel **ZT-257**

50Ω 0.5 to 6 GHz SMA Female

TYPICAL PERFORMANCE CURVES











4 x 4-Way Splitter/Combiner Panel **ZT-257**

50Ω 0.5 to 6 GHz SMA Female

OUTLINE DRAWING





OUTLINE DIMENSIONS (Inch)

Α	В	С	D	Ε	F	G	Н	J	K	L	M	N	Р	Q	weight
1.73	19.00	3.75	0.13	1.76	15.48	1.250	18.330	0.94	2.20	0.50	1.30	2.10	2.60	4.00	grams
43.9	482.6	95.3	3.3	44.7	393.19	31.75	465.6	23.9	55.9	12.7	33.0	53.3	66.0	101.6	1000



4 x 4-Way Splitter/Combiner Panel **ZT-257**

50Ω 0.5 to 6 GHz SMA Female

ORDERING INFORMATION

To learn more, click here: ZT-257

Model	Description
ZT-257	4 x 4-Way Splitter/Combiner Panel

Included Accessories	Part No.	Description
	HT-4-SMA	SMA Cable Wrench (4 in)

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

