Wideband, DC Pass Directional Couplers ZUDC-Series

Up to 20W 10, 15, 20, and 30 dB 2 to 18 GHz 50Ω

The Big Deal

- Wideband, 2 to 18 GHz
- Excellent Coupling Flatness, ±0.4 dB typ.
- Power Handling up to 20W



CASE STYLE: HT2628

Product Overview

The Mini-Circuits ZUDC family of wideband directional couplers offers exceptional performance spanning frequencies from 2 to 18 GHz. Available in models with 10, 15, 20, and 30 dB coupling, these couplers provide excellent coupling flatness, good directivity, and power handling up to 20W. They are ideal for lab testing applications as well as for power monitoring over wide bands, among other applications.

Key Features

| Feature | Advantages |
|--|---|
| Wide bandwidth | With a bandwidth spanning 2 to 18 GHz, ZUDC couplers are ideal for most lab testing applications, avoiding the need to switch components for different frequency bands. |
| Excellent Directivity • 17 dB typ. up to 18 GHz | High directivity allows sampling of input powers with minimal detrimental effects due to output mismatches. |
| Excellent coupling flatness • +0.4 dB typ. up to 18 GHz | Excellent coupling flatness over the entire frequency range eliminates the need for compensation circuits in most cases. |
| Good Return Loss • 15 dB typ. up to 18 GHz | Good return loss over 2 to 18 GHz minimizes undesired reflections and resulting ampli- tude ripple. |

- A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Notes

Wideband, DC Pass **Directional Coupler**

Up to 20W 50Ω **10dB**


Maximum Ratings

| Operating Temperature | -55°C to 85°C | |
|---|----------------|--|
| Storage Temperature | -55°C to 100°C | |
| Supplied Termination* | 1W | |
| * Up to 50°C derate linearly to 350 mW at 100°C | | |

Permanent damage may occur if any of these limits are exceeded

Coaxial Connections


| INPUT | IN |
|----------------------------|-----|
| OUTPUT | OUT |
| COUPLED | CPL |
| TERMINATION (50Ω) INCLUDED | _ |




Outline Dimensions (inch)

| A | B | C | D | E | |
|-------|-------|--------|------|-------|--|
| 2.25 | 0.73 | 0.50 | 0.38 | 1.50 | |
| 57.15 | 18.54 | 12.70 | 9.65 | 38.10 | |
| F | G | H | | wt | |
| 0.10 | 0.30 | #4-40 | | grams | |
| 2.54 | 7.62 | UNC-2B | | 40 | |

Electrical Schematic DIRECTIONAL COUPLER (DC THRU)





2 to 18 GHz

Features

- Wide frequency range, 2 to 18 GHz
- Good coupling flatness, ±0.4 dB typ.
- · Good directivity, 17 dB typ. up to 18 GHz
- . Good return loss, 15 dB typ. up to 18 GHz
- · DC current pass through input to output

Applications

- Cellular infrastructure
- Military
- Lab use

ZUDC10-02183-S+



CASE STYLE: HT2628

Connectors Model SMA-Fem ZUDC10-02183-S+


+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C

| Parameter | Frequency (GHz) | Min. | Тур. | Max. | Units |
|---|-----------------|------|------|-------|-------|
| Operating Frequency | | 2 | | 18 | GHz |
| Nominal Coupling | 2 – 18 | _ | 10±1 | — | dB |
| Coupling Flatness | 2 – 18 | _ | ±0.4 | ±0.65 | dB |
| Mainline Loss | 2 – 18 | _ | 0.3 | 1.5 | dB |
| Directivity | 2 – 18 | 15 | 25 | _ | dB |
| Return Loss (In & Out) | 2 – 18 | 14 | 26 | _ | dB |
| Return Loss (Coupling) | 2 – 18 | 14 | 26 | _ | dB |
| Input Power** | 2 – 18 | _ | _ | 20 | W |
| *I In to 95°C devote linearly to 12 7W at 100°C | | | | | · |

8.7W at 100°C

Mainline Loss Coupling Directivity **Return Loss** Frequency (dB) (dB) (dB) (MHz) (dB) In-Out Out In-Cpl In Cpl 2000 0.2 10.7 28.4 36.9 39.9 40.5 3000 0.3 10.8 26.0 21.5 21.6 21.8 4000 0.3 10.8 31.0 25.3 24.5 43.0 6000 20.1 19.9 32.5 0.4 10.5 24.2 8000 0.4 10.3 23.8 38.8 35.1 28.2 10000 20.3 24.2 0.5 23.6 20.7 10.3 12000 18.1 26.5 23.3 26.2 0.5 10.1 14000 0.6 10.2 24.9 25.5 21.6 24.1 16000 10.5 24.1 22.4 0.6 18.3 19.7 18000 10.8 23.0 14.7 20.5 19.7 0.7





 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement
C. The parts covered by this specification document are subject to Mini-Circuit's etandered limited test performance. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuit standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

REV. C ECO-016429 ZUDC10-02183-S+ WP/CP/AM 230119 Page 2 of 2

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Typical Performance Data

| Return Loss (In & Out) |
|------------------------------------|
| Return Loss (Coupling |
| Input Power** |
| **Up to 85°C derate linearly to 13 |
| |
| |

Mini-Circuits