

Coaxial

High Power Amplifier

ZHL-100W-251-S+

50Ω 100W 50 to 250 MHz

The Big Deal

- Output Power at Saturation 100W typ.
- Wide bandwidth, 50 to 250 MHz
- High gain, 46 dB typ.
- Good gain flatness, ± 0.7 dB typ.
- Unconditionally stable
- Self protected against high case temperature and shorting/unshorting of the DC supply
- Can withstand short and open circuit at output while delivering 100 watts



ZHL-100W-251-S+

Product Overview

The ZHL-100W-251+ is a Class A, high-power amplifier providing 100W saturated power over the 50 to 250 MHz band, ideal for a variety of high-power test setups as well as applications including communications, HAM bands and more. The ruggedly-designed amplifier provides unconditional stability and built-in self-protection against overheating. It is capable of withstanding short and open circuits at output while continuously delivering 100W of power. Housed in a rugged aluminum alloy case measuring 3.25 x 6.0 x 1.13", the unit features SMA connectors and heat sink and fan attachment for cooling.

Key Features

Feature	Advantages
Wideband, usable from 20 to 450 MHz	Suitable for a broad range of high-power, wideband applications, including test setups, HAM communication and defense applications.
High gain, 46 dB	Enables signal amplification to 100W output without the need for multiple gain stages.
Good gain flatness, ± 0.7 dB	Provides consistent performance across frequency without the need for gain flattening using external components.
Built-in self-protection	In instances of potentially-damaging heat buildup within the housing, unshorting of DC supply, and short or open loads at the output, an automatic sensing feature signals the unit to power down.
Unconditional stability	Provides reliable performance independent of input and load conditions.



High Power Amplifier

ZHL-100W-251-S+

50Ω 100W 50 to 250 MHz

Features

- High power, 100 Watt at saturation
- Usable over 20 to 450 MHz
- High gain, 46 dB typ.
- Excellent gain flatness, ± 0.7 dB typ.
- Excellent IP3, +58 dBm typ.
- Class A amplifier, usable up to 100W
- No damage with an open or short output load under full CW output power¹
- Shuts off when base plate temperature exceeds +100°C
- Internal power regulator (current remains constant over 22 to 28V)
- Over voltage protection, shut off above 29V



Case Style: BT1165

Connectors Model No.

SMA

ZHL-100W-251-S+

Applications

- VHF/UHF transmitters
- Defense
- Amateur radio, FM, TV
- Laboratory use

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	ZHL-100W-251-S+			Units
	Min.	Typ.	Max.	
Frequency Range	50		250	MHz
Gain	42	46	51	dB
Gain Flatness	—	± 0.7	± 1.5	dB
Output Power at 1dB compression	—	+48	—	dBm
Output Power at 3dB compression	—	+50	—	dBm
Noise Figure	—	4.5	—	dB
Output third order intercept point	—	+58	—	dBm
Input VSWR	—	1.4	—	:1
Output VSWR	—	2.5	—	:1
DC Supply Voltage	—	24	25	V
Supply Current	—	—	10.5	A

1. At constant open or short load 24V nominal supply voltage.


Maximum Ratings

Parameter	Ratings
Operating Temperature (with Mini-Circuits' heatsink and fan)	-20°C to 65°C
Storage Temperature	-55°C to 100°C
Input RF Power (no damage) ²	+9 dBm

2. At nominal output load, 24V nominal supply voltage. Limiter VLM-52-S+ is recommended to be used at the input of the amplifier.

Permanent damage may occur if any of these limits are exceeded.







Outline Drawing for models with heatsink



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt
9.85	7.3	6.3	6.00	1.00	3.75	.13	—	.25	.63	1.03	—	—	3.25	.5	6.00	5.1	.135	grams
250.19	185.42	160.02	152.40	25.40	95.25	3.30	—	6.35	16.00	26.16	—	—	82.55	12.70	152.40	129.54	3.43	4185

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		POUT at 1 dB COMPR. (dBm)	POUT at 3 dB COMPR. (dBm)	NOISE FIGURE (dB)	OIP3 (dBm)
	24V	24V	IN	OUT	24V	24V	24V	24V
50	46.1	38	1.77	3.33	48.7	49.7	4.3	58.6
70	46.2	36	1.68	2.94	48.7	49.8	4.1	58.5
100	46.2	30	1.59	2.81	49.6	50.2	3.9	58.6
130	46.5	37	1.49	2.54	49.6	50.4	3.9	59.1
150	46.2	49	1.46	2.36	49.6	50.4	3.9	59.7
180	46.7	33	1.42	2.25	49.4	50.3	3.9	59.3
200	45.8	35	1.41	2.15	48.9	50.1	3.9	58.7
220	45.6	33	1.40	2.18	48.1	49.9	4.0	58.1
250	45.5	53	1.38	2.27	47.6	49.6	4.0	58.1



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp