Cavity **Bandpass Filters**

50Ω DC to 50 GHz

The Big Deal

- · Very low insertion loss with excellent power handling
- Very fast roll-off with wide stopband
- · Passbands up to 36 GHz
- Stopbands up to 50 GHz



Product Overview

Mini-Circuits' cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 1% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.

Mini-Circuits' cavity filters feature a special protective assembly to prevent accidental de-tuning that would otherwise require expensive replacement or return to factory for re-tuning. Custom integrated assembly with LNA and bias tees results in greatly simplifying system integration. Precise machining allows realization of cavity filters with small form factors for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitter
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide spur free band results in better receiver sensitivity
High power handling	Well suited for transmitter application
Protective assembly	Prevents accidental de-tuning of precisely tuned resonant circuit

Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. The parts covered by this specification document are subject to Mini-Circuit's charadral limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial **Bandpass Cavity Filter**

50Ω 902 to 915 MHz

Features

Applications

Receivers/Transmitters

- Low Insertion loss, 2.0 dB typ.
- · Good VSWR, 1.2:1 typ. in passband
- · Narrow bandwidth with high selectivity

· CDMA band rejection for GSM base station






Generic photo used for illustration purposes only CASE STYLE: KT1510 Connectors Model SMA-F ZVBP-909-S+


Electrical Specifications at 25°C

Parar	neter	F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	—	—	_	908.5	—	MHz
Pass Band	Insertion Loss	F1-F2	902 - 915	_	2.0	2.7	dB
	VSWR	F1-F2	902 - 915	-	1.2	1.4	:1
Sten Band Lawer	Insertion Loss	DC-F3	10 - 895	20	33	_	dB
Stop Band, Lower	VSWR	DC-F3	10 - 895	_	30	—	:1
Stop Band, Upper	Insertion Loss	F4-F5	925 - 2300	20	34	-	dB
	VSWR	F4-F5	925 - 2300	_	25	_	:1

Functional Schematic



Typical Frequency Response




(MHz)	(dB)	(:1)	(:1)	
10.00	104.69	1737.18	1737.18	
870.00	98.08	289.53	289.53	
888.00	61.26	108.58	108.58	
895.00	33.04	34.07	37.77	
897.50	17.32	14.50	17.05	
899.00	6.81	5.25	6.21	
900.00	3.15	2.09	2.37	
902.00	1.85	1.14	1.09	
908.50	1.44	1.10	1.15	
915.00	1.77	1.17	1.18	
918.00	3.98	1.65	1.24	
919.00	9.87	3.58	2.55	
920.00	18.20	10.56	7.94	
925.00	47.86	43.44	41.37	
929.00	63.41	64.35	64.35	
950.00	102.83	157.93	157.93	
1300.00	103.35	434.30	434.30	
2300.00	98.96	193.02	248.17	

Typical Performance Data at 25°C

VSWR-In

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Maximum Ratings

*Derate linearly to 5 W at 100°C Permanent damage may occur if any of these limits are exceeded. Input and output ports are DC short to ground.

-55°C to 100°C -55°C to 100°C


15W max. at 25°C

Insertion Loss

Operating Temperature

Frequency

Storage Temperature **RF** Power Input*



VSWR-Out

Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectived), "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and meredies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV.C ECO-011269 ZVBP-909-S+ EDU-1316/1 URJ/NY 220318 Page 2 of 3

ZVBP-909-S+

Coaxial Connections

PORT - 1	SMA FEMALE
PORT - 2	SMA FEMALE

Outline Drawing



Outline Dimensions (inch)

93	9.59	2.637	9.893	F 0.236 5.99	0.150	0.300	1.150	3.110	10.193
าร	gran	0.638	0.638	Q 9.250 234.95	0.150	2.349	0.761	0.577	0.127

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits