

Coaxial Amplifier

ZVE-ED13284/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BN1327

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	1900		8100	MHz
Gain		34		dB
Output Power @ 1dB Compression		35		dBm
Noise Figure		5.7		dB
IP3		42		dBm
VSWR	IN	2.00		(:1)
	OUT	2.00		(:1)
DC Power	Voltage	12		V
	Current		2000	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 65°C
Storage Temperature	-65°C to 150°C
Input Power	20dBm