

Coaxial Amplifier

ZHL-ED13288

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : BT1344

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	700		2500	MHz
Gain		50		dB
Output Power @ 1dB Compression		44		dBm
Noise Figure		5.5		dB
IP3		50		dBm
VSWR	IN	1.30		(:1)
	OUT	1.20		(:1)
DC Power	Voltage	28		V
	Current		6300	mA

MAXIMUM RATINGS	
Operating Temperature	-20°C to 60°C
Storage Temperature	-55°C to 100°C
Input Power	0dBm