# Suspended Substrate Stripline Filters and Multiplexers

50Ω DC to 26 GHz

## The Big Deal

- Low insertion loss
- Ultra-wide passband width •
- Fast roll-off with wide stopband
- Good power handling and temperature stability
- Passband up to 26 GHz •
- Stopband up to 26.5 GHz can extend to 40 GHz

## Product Overview

Mini-Circuits' Suspended Substrate Stripline filters offer low insertion loss by implementing printed circuit board suspended between two parallel ground planes, providing high Q. Low insertion loss combined with wide stopband makes them an excellent choice for wideband instruments and systems like ECM, ECCM, ELINT and ultrabroadband receivers.

Low pass, high pass, band pass, band stop, diplexer and multiplexer designs can be realized with this technology. Advanced filter design and construction can achieve stopband width greater than 6x the center frequency, and temperature stability will be better than other printed circuit realizations because the fields are mainly in the air rather than in a dielectric. The inside walls of the housing hold the circuit and prevent movement that could be caused by vibration or mechanical shock, making these designs excellent candidates for harsh operating environments.

Suspended substrate stripline filters can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

# **Key Features**

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitters
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide, spur-free stop band results in better receiver sensitivity
High power handling	Well suited for transmitter applications
Excellent temperature stability	Ensures minimal variation in electrical performance across temperature

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Min-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits and and imited warranty and terms and conditions (collectivity, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

## Mini-Circuits

# Suspended substrate stripline **High Pass Filter**

50Ω

8000 to 24000 MHz


#### **Features**

- · Wider passband
- · Low insertion loss
- · Sharp rejection
- Connectorized package


### **Applications**

- Satellite communications
- Transmitter / Receiver
- X-band Radar
- KU-band Satellites

#### **Functional Schematic**



### **Typical Frequency Response**





Electrical Specifications at 25°C									
Parameter		F# Frequency (MHz)		Min.	Тур.	Max.	Unit		
		DC-F1	DC-4000	60	85	-	dB		
Stop Band	Rejection Loss	F1-F2	4000-5300	40	50	-	dB		
Stop Ballu		F2-F3	5300-5800	20	30	-	dB		
	VSWR	DC-F3	DC-5800	-	20	-	:1		
Pass Band	Insertion Loss	F4-F5	8000-24000	-	1	2	dB		
Fass Ballu	VSWR	F4-F5	8000-24000	-	2	-	:1		


Maximum Ratings							
Operating Temperature -40°C to 85°C							
Storage Temperature	-55°C to 100°C						
RF Power Input	3 W @ 25°C						
Permanent damage may occur if any of these limits are exceeded.							

#### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	99.20	19157.23
100	90.65	6188.96
1000	101.93	629.55
2500	91.16	205.38
4000	88.11	119.10
5300	76.20	85.04
5800	55.95	68.97
6000	48.29	60.82
6450	30.19	36.74
6650	21.37	23.94
6900	9.62	8.08
7050	3.93	2.80
7500	1.04	1.14
8000	0.94	1.51
9000	0.91	1.71
10000	0.67	1.53
12500	0.42	1.21
15000	0.76	1.80
20000	0.64	1.53
24000	0.71	1.68







/SWR

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.C ECO-008564 ZHSS-8G-S+ EDU2657/1 URJ 210629 Page 2 of 3

# ZHSS-8G-S+



Generic photo used for illustration purposes only

CASE STYLE: RP2464 Connectors Model SMA-M ZHSS-8G-S+


	<b>Mini-Circuits</b> °	
unum ministrum de serve	BO D. 050400 D. 11 . NV 44005 0000 (740) 004 4500	

ZHSS-8G-S+

### **Coaxial Connections**

PORT - 1	SMA-Male
PORT - 2	SMA-Male

#### **Outline Drawing**



### Outline Dimensions ( inch )

А	В	С	D	Е	F	G	н	J	к	Wt.
Max	Max	Max	-	-	-	-	-	-	-	
.70	.50	.50	.25	.25	.43	.350	.25	.170	.065	grams 30
17.78	12.70	12.70	6.35	6.35	10.92	8.89	6.35	4.32	1.65	00

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's tandard Terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

# **Mini-Circuits**