

# Power Splitter/Combiner

## ZX10-ED13246A/1

### 2 Way-0°

#### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : FL905

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		500		2500 MHz
Isolation	500-2500 MHz		24.3	dB
Insertion Loss Above 3.0 dB	500-2500 MHz		0.85	dB
Phase Unbalance	500-2500 MHz		0.70	deg.
Amplitude Unbalance	500-2500 MHz		0.01	dB
VSWR	SUM Port			(:1)
	OUT Ports			(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	3
PORT 1 (90°)	1
PORT 2 (0°)	2

#### electrical schematic

