

Coaxial Amplifier

ZX60-ED16053/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : 99-01-1803

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	410		450	MHz
Gain		22		dB
Output Power @ 1dB Compression		26		dBm
Noise Figure		0.9		dB
IP3		39		dBm
VSWR	IN	1.10		(:1)
	OUT	1.10		(:1)
DC Power	Voltage	25		V
	Current		220	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Input Power	+10dBm