

Power Splitter/Combiner ZN4PD1-ED12277/1

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : UU846

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1800		6400 MHz
Isolation	1800 - 6400 MHz		26	dB
Insertion Loss Above 6.0 dB	1800 - 6400 MHz		0.70	dB
Phase Unbalance	1800 - 6400 MHz		1.170	deg.
Amplitude Unbalance	1800 - 6400 MHz		0.099	dB
VSWR	SUM Port		1.20	(:1)
	OUT Ports		1.15	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	3
PORT 1	1
PORT 2	2
PORT 3	4
PORT 4	5

Functional Diagram

