Coaxial Reflectionless Low Pass Filter

50 Ω DC to 20 GHz

The Big Deal

- Patented design terminates stopband signal internally
- Stopband performance up to 40 GHz
- Small In-line package size of 0.80" x 0.56"



ZXLF-Series

CASE STYLE: RA2937

Product Overview

Mini-Circuits' ZXLF Series of reflectionless filters employ a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. Reflectionless filters minimize the stopband reflections, thereby allowing them to be paired with sensitive devices and be used in applications that otherwise require circuits such as isolation amplifiers or attenuators. This is developed in a new broadband connectorized package that delivers stable performance over temperature.

Key Features

Feature	Advantages
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect pass band signals.
Excellent stability over temperature	Ensures minimal variation in electrical performance across temperature.
Wide Operating temperature from -40 to +85°C	Suitable for use in wide temperature range applications.
Broadband connectorized package	The connectorized package works well even in high frequencies and easy to interface with other devices. This is well suited for test setups.

Coaxial Reflectionless Low Pass Filter

50Ω DC to 17 GHz


Features

- Match to 50Ωin the stop band,
- eliminates undesired reflections
- Cascadable
- Temperature stable, up to 85°C
- Protected by US Patent No. 8,392,495

Applications

- Harmonics Rejection
- Satellite
- Radar
- Military & Space

Functional Schematic



Specification Definition

FREQUENCY (MHz)

F5

F4

F1F2 F3

NSERTION LOSS (dB)

DC

Absolute Maximum Ratings³

Insertion Loss

Freq. Cut-off

VSWR

VSWR

Rejection

Parameter

Pass Band

Stop Band

	-	
Operating Temperature	-40°C to +85°C	
Storage Temperature	-55°C to +100°C	
RF Power Input, Passband (DC-F1) ¹	2W at 25°C	
RF Power Input, Stopband (F2-F5) ²	30mW at 25°C	

DC-F1

F2

DC-F1

F3-F4

F4-F5

F3-F4

F4-F5

¹ Passband rating derates linearly to 1W at 85°C ambient

 $^{\rm 2}$ Stopband rating derates linearly to 15mW at 85 $^{\circ}C$ ambient


³ Permanent damage may occur if any of these limits are exceeded


ESD rating

Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD 5.1 - 2001

Typical Performance Data at 25°C

Typical i chomanoc Data at 20 C			
Frequency (GHz)	Insertion Loss (dB)	VSWR (:1)	
10	0.31	1.03	
100	0.34	1.02	
500	0.43	1.03	
1000	0.51	1.08	
2000	0.65	1.16	
4000	0.83	1.19	
6000	0.96	1.12	
10000	1.27	1.10	
13000	1.56	1.18	
17000	2.51	1.48	
18000	3.11	1.78	
20000	5.16	2.41	
25000	33.40	2.87	
30000	23.33	2.64	
35000	35.07	5.11	
40000	22.27	7.12	





REV. OR ECO-004178 ZXLF-K173+ AD/CP/AM 200922 Page 2 of 3

Generic photo used for illustration purposes only

ZXLF-K173+

2.92mm-F to 2.92mm-M	ZXLF-K173+
Connectors	Model
CASE STYLE: R	A2937

2.3

3.0

14

25.0

22.0

3.0

5.8

18.0

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Max.

2.8

Unit

dB

dB

:1

dB

dB

:1

:1

Electrical Specifications at 25°C F# Frequency (MHz) Min. Тур. DC-17000

18000

DC-17000

25000-35000

35000-40000

25000-35000

35000-40000

Mini-Circuits		
www.minicircuits.com	P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com	


Low Pass Filter

ZXLF-K173+

Coaxial Connections

PORT - IN	2.92mm-Fem
PORT - OUT	2.92mm-Male

Outline Drawing



Additional Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp