



Mini-Circuits

RACK-MOUNTED

Adapter Patch Panel

ZT-427BK


50Ω DC to 6 GHz 24 x SMA Female to 4.3/10 Female

KEY FEATURES


- Rack-mounted connector patch panel
- 24 x SMA to 4.3/10 adapters in 3U rack space
- Excellent return loss
- Flat frequency response

APPLICATIONS

- Production test setups
- 4G & 5G FR1 radio testing
- Simplification of cable runs
- Interconnection of RF cables & equipment



Front View



Rear View

Generic photo used for illustration purposes only

PRODUCT OVERVIEW



Mini-Circuits panel-mounted structures provide clean, organized management of cable runs and connections in complex, high volume test setups. Multiple connector adapters, power splitters, directional couplers and other essential RF components and test accessories can be integrated efficiently within the test system. Custom configurations are available upon request.

ZT-427BK integrates 24 wideband adapters on to a compact panel requiring only 3U of rack space, with SMA female connectors on the front and high reliability 4.3/10 female connectors on the rear.

ELECTRICAL SPECIFICATIONS AT +25°C (EACH ADAPTER)

Parameter	Conditions (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		6	GHz
Insertion Loss	DC to 6		0.1		dB
Return Loss	DC to 6	20			dB

TYPICAL PERFORMANCE GRAPHS



Mini-Circuits



RACK-MOUNTED


Adapter Patch Panel

ZT-427BK

Mini-Circuits

50Ω DC to 6 GHz 24 x SMA Female to 4.3/10 Female

CASE STYLE DRAWING



PRODUCT MARKING*

Unit ID Label: Serial number and other identification marks

*Marking may contain other features or characters for internal lot control



Mini-Circuits

RACK-MOUNTED

Adapter Patch Panel

ZT-427BK

50Ω DC to 6 GHz 24 x SMA Female to 4.3/10 Female

ABSOLUTE MAXIMUM RATINGS

Parameter	Conditions	Limits	Units
Temperature	Operating	0 to +50	°C
	Storage	-20 to +60	

Permanent damage may occur if any of these limits are exceeded. Operating in the range between operating power limits and absolute maximum ratings for extended periods of time may result in reduced life and reliability.

CONNECTIONS

Port	Connector
01-24 (front)	SMA female
01-24 (rear)	4.3/10 female

DETAILED MODEL INFORMATION IS AVAILABLE ON OUR WEBSITE [CLICK HERE](#)

Case Style	99-01-3729	
Environmental Rating	ENV55	
Regulatory Compliance	Refer to our website for compliance methodologies and qualifications  	www.minicircuits.com/quality/environmental_introduction.html

Contact Us: testsolutions@minicircuits.com

Included Accessories	Part Number	Description
	HT-4-SMA	SMA connector wrench (4" length)

- NOTES
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

