



NEW



Rugged, portable, production test workhorses


Sweep or hop across wide frequency and power bands, use a pair for third-order intercept tests, or slip one into your laptop case and take it on the road! Our easy-to-use GUI will have you up and running in minutes. Compatible with most test software,* they add capabilities and increase efficiency, all without busting your budget!

Accurate, reliable results at high speed


Signals within 1 ppm for frequency and 0.25 dBm for power, low harmonics, a resolution of 5 kHz, and 5-msec settling times help you get the data you need from complex, high-speed testing plans. Just go to minicircuits.com for specifications, performance data, and everything you need to make your choice — and get it in your hands as soon as tomorrow!

*See data sheets for an extensive list of compatible software.

Model	Frequency (MHz)	Power (dBm)	Harmonics (dBc typ.)	Price (\$ ea.)
SSG-4000HP	250-4000	-50 to +20	-40	1995.00
SSG-4000LH	250-4000	-60 to +10	-66	2395.00



Frequency and power hopping.



Low spurious.

Smart SYNTHESIZED SIGNAL GENERATORS 250-4000 MHz only **WOW! \$1995⁰⁰ ea.**

