## Cavity **Bandpass Filters**

DC to 15 GHz  $50\Omega$ 

### **The Big Deal**

- Very low insertion loss with excellent power handling
- Very fast roll-off with wide stopband
- Passbands up to 15 GHz
- Stopbands up to 22 GHz



#### **Product Overview**

Mini-Circuits' cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 1% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.

Mini-Circuits' cavity filters feature a special protective assembly to prevent accidental de-tuning that would otherwise require expensive replacement or return to factory for re-tuning. Precise machining allows realization of cavity filters with small form factors for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

### **Key Features**

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitter
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide spur free band results in better receiver sensitivity
High power handling	Well suited for transmitter application
Protective assembly	Prevents accidental de-tuning of precisely tuned resonant circuit

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Puchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# **Bandpass Filter**

 $50\Omega$ 10700 to 12750 MHz

## ZVBP-11R7G-S+



Generic photo used for illustration purposes only

CASE STYLE: UG2852 Connectors Model

ZVBP-11R7G-S+

#### Electrical Specifications at 25°C


Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	Fc	-	-	11725	-	MHz
Pass Band	Insertion Loss	F1-F2	10700 - 12750	-	1.0	2.0	dB
	VSWR	F1-F2	10700 - 12750	-	1.50	1.76	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 10200	43	54	-	dB
Stop Band, Upper	Insertion Loss	F4-F5	13200 - 20000	35	46	-	dB

Maximum Ratings				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	10 W			


Permanent damage may occur if any of these limits are exceeded


#### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)	
100	85.92	782.93	10700	2.52	
500	96.28	226.13	10800	2.51	
1000	120.05	177.34	10900	2.10	
5000	103.35	133.63	11000	1.83	
10000	71.20	98.13	11100	1.69	
10200	55.18	84.58	11200	1.60	
10420	30.99	55.86	11300	1.54	
10490	20.43	35.57	11400	1.50	
10590	3.04	3.36	11500	1.46	
10700	0.69	1.36	11600	1.44	
11000	0.61	1.45	11700	1.43	
11725	0.58	1.47	11725	1.42	
12000	0.49	1.26	11900	1.43	
12750	0.64	1.05	12000	1.45	
12860	3.54	4.14	12100	1.48	
12970	20.34	35.77	12200	1.53	
13050	30.83	48.08	12300	1.59	
13200	46.22	70.54	12400	1.68	
16000	99.81	87.48	12500	1.84	
20000	94.63	95.09	12750	2.38	










## **Features**

- · Low insertion loss, 1 dB typical
- Broad stopband performance upto 20 GHz
- · High rejection


#### **Applications**

- · Fixed and satellite communication
- Mobile communication
- Broadcasting satellite

#### **Functional Schematic**



#### **Typical Frequency Response**



#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

2.8 2.6

2.4

2.2 XX 2.0 1.8 1.8 1.4

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

FREQUENCY (MHz)


#### **Coaxial Connections**


PORT-1	SMA-Female
PORT-2	SMA-Female

#### **Outline Drawing**









#### Outline Dimensions (inch mm)

F	E	D	С	В	Α
.495	.18	2.347	.44	.70	2.70
12.57	4.4	59.61	11.2	17.7	68.5
Wt.		K	J	н	G
grams		.35	.20	.100	.10
75		8.8	5.0	2.54	2.5

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please vist Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp