## Cavity **Bandpass Filters**

**50**Ω DC to 15 GHz

## **The Big Deal**

- Very low insertion loss with excellent power handling
- Very fast roll-off with wide stopband
- · Passbands up to 15 GHz
- Stopbands up to 20 GHz



## Product Overview

Mini-Circuits' cavity filters are designed by implementing resonant structures with very high Q and are ideal for narrow-band, high-selectivity applications. These designs can provide bandwidths as narrow as 1% with very high selectivity and excellent low noise floor. Low insertion loss combined with excellent power handling makes them well-suited for transmitter and receiver front end. Advanced filter design and construction enables stopband width greater than 3x the center frequency.

Mini-Circuits' cavity filters feature a special protective assembly to prevent accidental de-tuning that would otherwise require expensive replacement or return to factory for re-tuning. Precise machining allows realization of cavity filters with small form factors for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## **Key Features**

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in receiver front end and better power delivery to antenna in transmitter
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stopband	Wide spur free band results in better receiver sensitivity
High power handling	Well suited for transmitter application
Protective assembly	Prevents accidental de-tuning of precisely tuned resonant circuit

A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. G. The parts covered by this specification document are subject to Mini-Circuits trandard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



# Cavity **Bandpass Filter**

50Ω 2030 to 2115 MHz


#### **Features**

- · Low insertion loss
- High rejection
- Connectorized package


#### **Applications**

- Fixed communication
- · Space research
- Mobile communication

#### **Functional Schematic**



#### **Typical Frequency Response**






Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	Fc	2072.5	-	0.5	-	dB
Pass Band	Insertion Loss	F1-F2	2030 - 2115	-	0.6	1.2	dB
	VSWR	F1-F2	2030 - 2115	-	1.28	1.5	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 1930	40	48	-	dB
	VSWR	DC-F3	DC - 1930	-	20	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	2220 - 6000	40	49		dB
	VSWR	F4-F5	2220 - 6000	-	20	-	:1

Maximum Ratings						
Operating Temperature	-40°C to 85°C					
Storage Temperature	-55°C to 100°C					
RF Power Input	15 W max.					

Permanent damage may occur if any of these limits are exceeded.

#### Typical performance data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)	
10.0	74.33	1460.34	2025.0	17.83	
100.0	86.05	407.52	2030.0	15.19	
400.0	89.41	184.49	2035.0	13.45	
700.0	100.40	177.21	2040.0	12.53	
1930.0	49.35	312.98	2045.0	11.93	
1977.0	30.19	150.66	2050.0	11.45	
1993.0	20.67	75.54	2055.0	11.07	
2015.0	3.44	4.36	2060.0	10.83	
2025.0	0.62	1.04	2065.0	10.71	
2030.0	0.57	1.22	2072.5	10.65	
2072.5	0.42	1.00	2075.0	10.64	
2073.5	0.42	1.02	2080.0	10.64	
2115.0	0.58	1.25	2085.0	10.71	
2131.0	3.08	3.83	2090.0	10.89	
2153.0	20.10	53.36	2095.0	11.20	
2171.0	30.63	97.52	2100.0	11.64	
2220.0	49.80	188.11	2105.0	12.15	
2400.0	83.46	379.71	2110.0	12.84	
5200.0	108.39	162.21	2115.0	14.07	
6000.0	101.33	171.58	2120.0	16.29	



Notes A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

### ∭Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV OR M172656 ZVBP-2072R5-S+ EDU3480 URJ 190919 Page 2 of 3

## ZVBP-2072R5-S+



Generic photo used for illustration purposes only CASE STYLE: QT2302 Connectors Model ZVBP-2072R5-S+ SMA-F

ZVBP-2072R5-S+ INSERTION LOSS (Zoomed)

2100

2085

FREQUENCY (MHz)

2150

2110

0.40 0.50 0.60

2050 FREQUENCY (MHz)

2060

ZVBP-2072R5-S+

GROUP DELAY

07

#### Electrical Specifications at 25°C

2200


2135

ZVBP-2072R5-S+

#### **Coaxial Connections**

PORT - 1 SMA-Female PORT - 2 SMA-Female

#### **Outline Drawing**



#### Outline Dimensions ( inch )

			•				
Α	В	С	D	E	F	G	н
5.20	1.38	1.18	.08	4.59	4.19	.59	.31
132.00	35.00	30.00	2.00	116.50	106.34	15.00	8.00
					_		
J	K	L	M	N	Р		Wt.
.78	.750	4.960	.12	.22	.126		grams
19.84	19.05	125.98	3.01	5.47	3.20		184

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's tandard Terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

## **Mini-Circuits**