

Frequency Mixer

ZX05-ED12902/3

Level 7 (LO Power + 7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : FL905

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (f _L to f _U)	750		4200	MHz
	RF (f _L to f _U)	750		4200	MHz
	IF	10		1500	MHz
Conversion Loss	Total Range		6.3		dB
LO-RF Isolation			31		dB
LO-IF Isolation			21		dB
Input IP3			+12		dBm
1 dB Compression			+1		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

COAXIAL CONNECTIONS	
LO	2
RF	3
IF	1

Electrical Schematics

