

Up Converter Frequency Mixer

Level 17 (LO Power +17 dBm) 10 to 7100 MHz

ZX05-U712H-S+



Generic photo used for illustration purposes only

CASE STYLE: FL905

Connectors	Model
SMA	ZX05-U712H-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
IF Power	100mW
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

LO	1
IF (IN)	2
RF (OUT)	3

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.74	.90	.54	.50	.04	.16	.29
18.80	22.86	13.72	12.70	1.02	4.06	7.37
H	J	K	L	M	N	wt
.37	--	.122	.496	.106	.122	grams
9.40	--	3.10	12.60	2.69	3.10	20.0

Features

- up converter mixer
- low conversion loss, 7.5 dB typ.
- high IP3, 27 dBm typ.
- rugged construction
- small size
- protected by US patents, 6,790,049 and 7,027,795

Applications

- cellular infrastructure
- WIMAX
- line-of-sight links
- wide band receivers
- bluetooth

Electrical Specifications

FREQUENCY (MHz)			CONVERSION LOSS* (dB)			LO-IF (IN) ISOLATION (dB)		LO-RF (OUT) ISOLATION (dB)		IP3 at center band (dBm)
IF (IN)	LO	RF (OUT)	Typ.	σ^{**}	Max.	Typ.	Min.	Typ.	Min.	Typ.
2600-7100	10-1780	2600-7100	7.5	0.3	9.2	30	17	24	15	27

1 dB COMPR. +14 dBm typ.


* Conversion Loss at 30 MHz LO

** σ is a standard deviation

Typical Performance Data

Frequency (MHz)			Conversion Loss (dB)	VSWR RF Port (:1)	Frequency (MHz)	Isolation L-I (dB)	Isolation L-R (dB)	VSWR LO Port (:1)
IF (IN)	LO	RF (OUT)	LO +17dBm	LO +17dBm		LO +17dBm	LO +17dBm	LO +17dBm
2600.10	30.00	2630.10	7.83	1.32	10.10	69.72	54.09	1.33
2800.10	30.00	2830.10	7.15	1.47	100.10	51.66	38.75	1.32
3000.10	30.00	3030.10	6.97	1.61	200.10	45.94	34.10	1.38
3400.10	30.00	3430.10	7.08	2.07	300.10	41.85	31.17	1.48
3600.10	30.00	3630.10	7.22	2.23	400.10	39.69	28.59	1.60
3800.10	30.00	3830.10	7.51	2.42	500.10	37.41	26.06	1.62
4000.10	30.00	4030.10	7.43	2.55	600.10	35.37	24.40	1.62
4400.10	30.00	4430.10	7.48	2.77	700.10	34.28	22.62	1.63
4600.10	30.00	4630.10	7.18	2.72	800.10	32.48	21.55	1.67
4800.10	30.00	4830.10	7.28	2.65	900.10	31.01	21.20	1.80
5000.10	30.00	5030.10	7.20	2.62	1000.10	30.18	21.05	1.97
5200.10	30.00	5230.10	7.40	2.57	1100.10	28.34	20.83	2.20
5400.10	30.00	5430.10	7.53	2.46	1200.10	27.15	20.30	2.41
5600.10	30.00	5630.10	7.76	2.40	1300.10	26.11	19.80	2.56
5800.10	30.00	5830.10	7.81	2.16	1400.10	24.55	19.67	2.67
6000.10	30.00	6030.10	7.83	1.96	1500.10	23.55	19.71	2.76
6200.10	30.00	6230.10	7.55	1.73	1600.10	22.84	19.33	2.93
6400.10	30.00	6430.10	7.33	1.58	1700.10	21.54	18.71	3.00
6600.10	30.00	6630.10	7.09	1.59	1720.10	21.24	18.63	3.06
7100.10	30.00	7130.10	7.37	1.80	1780.10	20.77	18.34	3.08

Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/VCLStore/terms.jsp










www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M171494
ZX05-U712H-S+
ED-12902/18
DJ/CP/AM
200811
Page 1 of 2

Performance Charts

ZX05-U712H-S+



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

