

Power Splitter/Combiner

ZX10-ED13665/3

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : KB1450

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1500		18000 MHz
Isolation	1500-18000 MHz		20	dB
Insertion Loss Above 3.0 dB	1500-18000 MHz		1.00	dB
Phase Unbalance	1500-18000 MHz		2.90	deg.
Amplitude Unbalance	1500-18000 MHz		0.22	dB
VSWR	SUM Port		1.55	(:1)
	OUT Ports		1.50	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2

electrical schematic

