

Coaxial Amplifier

ZX60-ED12843/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : GC957

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	.5		4000	MHz
Gain		19.4		dB
Output Power @ 1dB Compression		17.3		dBm
Noise Figure		5.4		dB
IP3		33		dBm
VSWR	IN	1.20		(:1)
	OUT	2.00		(:1)
DC Power	Voltage	5		V
	Current		110	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Input Power	13dBm