



THE BIG DEAL

- Ultra-High Stopband Rejection Structure – 90 dB typical
- Surface mountable pick and place standard case style
- Standard small 1812 (4.5mm x 3.2mm) case style
- High quality distributed filter topology
- Wide rejection band
- Shielded construction preventing filter from de-tuning
- Reduced footprint area by employing LGA (land grid array)
- Suited for very high-volume production
- Protected by US Patents 11,638,370 and 11,744,057



Generic photo used for illustration purposes only

CASE STYLE: NM1812C-3

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Test and Measurement
- C-Band Satellite
- Aerospace and Defense Signal Conditioning

PRODUCT OVERVIEW

The BFHK-6751+ LTCC Band Pass Filter achieves a miniature size and high repeatability of performance by utilizing a proprietary LTCC material system and distributed filter topology. The passband loss at 5.9 – 6.9 GHz is as low as 3.1 dB, with typical stopband rejections at 90 dB up to 20 GHz. This model handles up to 1W RF input power, and provides a wide operating temperature range from -55 to +125°C. Utilizing a proprietary LTCC material system and a distributed filter topology, this filter is able to achieve repeatable performance on a lot-to-lot basis, up to mmWave frequencies.

KEY FEATURES

Feature	Advantages
Ultra-High Rejection	Typical stopband rejections at 90 dB up to 20 GHz
Cost effective	LTCC is scalable technology that is cost effective due to ease of production in high quantities.
Small size (4.5mm x 3.2mm)	Allows for high layout density of circuit boards, while minimizing effects of parasitics.
Surface Mountable	Suitable for very high volume automated assembly process.



CERAMIC

Bandpass Filter

BFHK-6751+

ELECTRICAL SPECIFICATIONS¹ AT 25°C

Parameter	F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Pass Band	Center Frequency	—	—	6.4	—	GHz
	Insertion Loss	F1-F2	—	3.1	5.0	dB
	Return Loss	F1-F2	—	12.0	—	dB
Stop Band, Lower	Insertion Loss	DC-F3	80.0	90.0		dB
Stop Band, Upper	Insertion Loss	F4-F5	80.0	90.0		dB


1. Measured on Mini-Circuits Test Board TB-BFHK-6751C+ with feedline losses removed by normalization of S12 and S21 traces to measurement of TB thru-line

MAXIMUM RATINGS


Parameter	Ratings
Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input	1W max.

Permanent damage may occur if any of these limits are exceeded

TYPICAL FREQUENCY RESPONSE



FUNCTIONAL SCHEMATIC







CERAMIC

Bandpass Filter

BFHK-6751+


EVALUATION BOARD MCL P/N: TB-BFHK-6751C+
SUGGESTED PCB LAYOUT: PL-730

NOTES:


1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
3. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

LAYER 2, B-VIA & PTH



LAYER 3 & PTH




PAD CONNECTIONS

INPUT	1
OUTPUT	2
GROUND	3

PRODUCT MARKING: F441

OUTLINE DRAWING



Weight: .126 grams.

Dimensions are in inches (mm). Tolerances: 2 Pl.±.01; 3 Pl. ±.005






CERAMIC

Bandpass Filter

BFHK-6751+

TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	92.24	0.03
1000	117.45	0.31
2000	112.11	0.29
3000	105.80	0.44
4000	91.43	0.57
5000	57.05	0.70
5900	2.90	14.36
6400	2.55	25.08
6900	3.08	21.27
8000	55.79	1.51
9200	97.42	0.91
10000	97.17	1.01
11000	98.19	1.22
12000	98.09	1.14
13000	96.02	1.07
14000	98.21	1.27
15000	98.85	1.46
16000	100.36	1.50
17000	105.41	1.51
18000	106.82	1.48
20000	106.56	1.75



- NOTES**
- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	92.24	0.03
50	94.56	0.07
100	103.06	0.10
500	117.57	0.25
1000	117.45	0.31
1500	105.77	0.30
2000	112.11	0.29
2500	103.54	0.35
3000	105.80	0.44
3500	97.94	0.53
4000	91.43	0.57
4500	78.00	0.59
5000	57.05	0.70
5500	19.16	2.15
5900	2.90	14.36
5950	2.80	15.17
6000	2.66	18.38
6050	2.57	24.21
6100	2.55	21.96
6150	2.58	17.77
6200	2.61	16.30
6250	2.61	16.53
6300	2.58	18.46
6350	2.55	22.27
6400	2.55	25.08
6450	2.59	21.98
6500	2.64	19.25
6550	2.70	18.24
6600	2.73	18.79
6650	2.76	20.71
6700	2.79	23.75
6750	2.84	24.87
6800	2.91	22.77
6850	2.99	21.27
6900	3.08	21.27
6950	3.16	22.71
7000	3.26	24.13
7500	6.71	20.75
8000	55.79	1.51
8500	91.03	1.07
9000	103.11	0.94
9200	97.42	0.91
9500	95.34	0.92
10000	97.17	1.01
10500	98.19	1.14
11000	98.19	1.22
11500	95.02	1.23
12000	98.09	1.14
12500	93.75	1.07
13000	96.02	1.07
13500	96.85	1.14
14000	98.21	1.27
14500	96.54	1.39
15000	98.85	1.46
15500	97.90	1.50
16000	100.36	1.50
16500	102.06	1.51
17000	105.41	1.51
17500	104.40	1.49
18000	106.82	1.48
18500	110.43	1.47
19000	111.79	1.51
19500	109.91	1.63
20000	106.56	1.75
21000	118.04	1.99
22000	60.50	2.91
23000	15.89	4.23
24000	22.13	2.80
25000	63.71	2.42
26000	72.65	2.60
27000	66.63	2.60
28000	66.29	2.47
29000	66.99	2.21
30000	65.99	1.95

Ceramic Bandpass Filter

BFHK-6751+

Typical Performance Curves




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS



REV. OR
BFHK-6751+
8/6/2021
Page 1 of 1



Weight: .126 grams.

Dimensions are in inches [mm]. Tolerances: 2 Pl. ±.01; 3 Pl. ±.005 Inches

Notes:

1. Case material: Ceramic.
2. Termination Finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin Plate over Nickel plate. All models, (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-013254	NEW RELEASE	05/16/22	ITG	IL
A	ECO-015587	UPDATED STACK-UP DIAGRAM	11/01/22	ITG	IL
B	ECO-020890	ADDED DIMENSIONS	02/16/24	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR NM1812C-3 CASE STYLE



STACK-UP DIAGRAM




1. TOTAL FINISHED THICKNESS $0.0228 \pm .004$.
2. B-VIA PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 2.
3. PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.
4. INDICATED PLUGGED PTH's ARE PLUGGED WITH EPOXY AND CAPPED WITH COPPER FROM TOP SIDE.
5. LAYER 4 IS CONTINUOUS GROUND PLANE.

NOTES:

1. PCB IS MULTILAYER PCB, SEE STACK-UP DIAGRAM.
2. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
3. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

ITG

05/16/22

CHECKED

GF

05/16/22

APPROVED

IL

05/16/22



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, NM1812C-3, TB-1239

SIZE

A

CODE IDENT

15542

DRAWING NO:

98-PL-730

REV:

B

FILE:

98PL730

SCALE:

8:1

SHEET:


1 OF 2

Mini-Circuits®



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

LAYER 2, B-VIA & PTH



LAYER 3 & PTH





THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA2.DWG REV:A DATE: 01/12/94


ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-730	B
FILE:	98PL730	SCALE: 8:1	SHEET: 2 OF 2

Evaluation Board and Circuit



Schematic Diagram



STACK-UP DIAGRAM

Notes:

1. 2.92 mm Female End Launch Connector.
2. PCB Material: Megtron 6 R5775(N).
Dielectric Constant=3.6.
3. Total finished thickness .019".

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Thermal Cycling	-55 to 125°C, 100 cycles, Dwell Time 15 minutes.	MIL-STD-202, Method 107, Condition A-3
Mechanical Shock	50g, 11ms half-sine, 18 shocks applied each to 3 axes	MIL-STD-202 Method 213, Condition A
Vibration	10-2000Hz sine, 20g, 12 cycles applied each to 3 axes	MIL-STD-202, Method 204, Condition D
Constant Acceleration	30Kg, Y1 Direction	MIL-STD-883, Method 2001, Condition E
Humidity	85°C, 90-95% Relative Humidity, 250hours	
Solderability	10X / 30X Magnification	J-STD-002C Test S, J-STD-002C Test S1
High Temp Storage	125°C, 250 hours	