

Coaxial Amplifier

ZX60-ED13494/4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : GA955

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	4000		5800	MHz
Gain		24		dB
Output Power @ 1dB Compression		10		dBm
Noise Figure		2.0		dB
IP3		23		dBm
VSWR	IN	1.60		(:1)
	OUT	1.50		(:1)
DC Power	Voltage	12		V
	Current		80	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Input Power	13dBm