Wideband Amplifier

ZX60-V82-S+

50 Ω **20 to 6000 MHz**

The Big Deal

- Ultra wideband
- High dynamic range:
 - +19dBm P1dB compression
 - +35dBm Output IP3



CASE STYLE: GC957

Product Overview

The ZX60-V82-S+ (RoHS compliant) is a very compact wideband amplifier covering 20 to 6000MHz with 13.5dB gain (at 2GHz). Housed in a rugged, cost effective unibody chassis, this amplifier supports a wide variety of applications requiring moderate power output, low distortion and 50 ohm matched input/output ports.

Key Features

Feature	Advantages					
Ultra Wide band high dynamic range	The ZX60-V82-S+ covers a wide spectrum of application frequencies from VHF through 'C' band. When combined with the output power and IP3, this amplifier supports a broad array of systems and test applications.					
Well Matched input / output ports	With typical input VSWR of 1.3:1 and output VSWR of 1.5:1 at 2GHz, the ZX60-V82-S+ can be used in cascade with many components and maintain minimal interaction or reflections.					
Very small size, 0.75" x 0.75'	The unique unibody construction enables the ZX60-V82-S+ to be used in compact designs.					
Unconditionally stable	No adverse effects due to loading of the input and output ports.					

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exciteve rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/WCLStore/terms.jsp

Wideband Amplifier

ZX60-V82-S+

20 to 6000 MHz 50Ω

Features

- Wideband, 20 to 6000 MHz
- Output power at 1dB compression, +19 dBm typ.
- Good output IP3, 35 dBm typ.
- Good VSWR
- Unconditionally stable
- Protected by US patents 6,790,049 & 6,943,629

Applications

- Base station infrastructure
- CATV & DBS
- MMDS & wireless LAN
- LTE
- Buffer amplifier
- PCS
- Test equipment



Case Style: GC957 Connectors Model SMA ZX60-V82-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Units	
Frequency Range		20		6000	MHz	
	100	13.5	15.2	16.8		
	1000		14.7			
Gain	2000	12.0	13.5	15.2	dB	
Gaill	3000		12.3		ub	
	4000	9.5	11.4	13.0		
	6000		9.1			
	100	17.0	19.0			
	1000	17.5	19.5			
Outrot Decree at 1 dD accessoration	2000	18.0	20.0			
Output Power at 1dB compression	3000		19.7		dBm	
	4000		19.4			
	6000		17.5			
	100		6.5	8.0		
	1000		6.7			
N · F	2000		6.8	8.4	dB	
Noise Figure	3000		6.9			
	4000		7.0			
	6000		7.7			
	100		38.5			
	1000		36.5			
	2000	33.0	35.0		dBm	
Output third order intercept point	3000		34.0			
	4000		33.5			
	6000		31.0			
	100		1.10			
	1000		1.15			
	2000		1.30	1.5		
Input VSWR	3000		1.30		:1	
	4000		1.30			
	6000		1.70			
	100		1.30			
	1000		1.40			
	2000		1.50	1.9	:1	
Output VSWR	3000		1.70	-		
	4000		1.70			
	6000		2.30			
Active Directivity	20-6000		11		dB	
DC Supply Voltage	20 0000	4.8	5.0	5.2	V	
DC Supply Current			100	120	mA	

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and emedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLstore/terms.jsp




Maximum Ratings

Parameter	Ratings		
Operating Temperature	-40°C to 85°C Case		
Storage Temperature	-55°C to 100°C		
DC Voltage	5.5 V		
Input RF Power (no damage)	20 dBm		
Power Consumption	840 mW		

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing





NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note $\underline{AN-40-10}$.

Outline Dimensions (inch mm)

WT.	R	Q	Р	Ν	М	L	K	J	Н	G	F	Ε	D	С	В	Α
GRAM	.106	.18	.37	1.00	.14	.22	.21	.33	.59	.45	.17	.04	1.18	.46	.75	.74
00.0	0.60	4 57	0.40	OF 40	0.50	E E0	E 00	0.00	1400	11 10	4 00	1 00	20.07	11 00	10.05	10.00


Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limit derms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and emedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR IN	VSWR OUT	POWER OUT @ 1dB COMPRESSION	OUTPUT IP3	NF (dB)
			(:1)	(:1)	(dBm)	(dBm)	
20	14.83	9.70	1.19	1.48	18.46	38.01	6.26
100	15.15	9.03	1.07	1.27	19.23	38.50	6.51
420	15.06	9.18	1.08	1.27	19.50	37.95	6.65
1000	14.66	9.33	1.15	1.35	19.51	36.39	6.73
1220	14.43	9.46	1.18	1.39	19.57	36.12	6.74
1420	14.21	9.61	1.20	1.42	19.67	35.86	6.74
1620	13.96	9.79	1.22	1.46	19.55	35.71	6.75
2000	13.49	10.09	1.26	1.53	19.81	35.12	6.77
2220	13.21	10.23	1.28	1.58	19.80	34.93	6.80
2420	12.97	10.44	1.29	1.61	19.70	34.67	6.83
2620	12.72	10.61	1.29	1.64	19.87	34.48	6.84
3000	12.30	10.92	1.30	1.69	19.71	34.27	6.88
3420	11.88	11.15	1.29	1.72	19.47	33.61	6.91
4000	11.36	11.48	1.25	1.71	19.40	33.64	7.00
4420	11.03	11.69	1.20	1.72	19.14	33.14	7.08
5000	10.48	12.18	1.20	1.83	18.72	32.41	7.27
5420	9.94	12.78	1.34	2.05	18.36	31.90	7.38
6000	8.96	14.10	1.68	2.44	17.34	31.22	7.65
6620	7.66	15.87	2.11	2.81	16.55	30.43	7.90
7000	6.73	17.14	2.38	2.92	16.35	30.15	8.19



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limit derms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and emedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp