## Coaxial

# Coaxial-Ceramic Resonator Filters and Multiplexers

DC to 6 GHz  $50\Omega$ 

# The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%</li>
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



## **Product Overview**

Mini-Circuits' Coaxial-Ceramic Resonator filters offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA in greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## **Key Features**

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.js



# **Bandpass Filter**

 $50\Omega$ 870 to 915 MHz

# ZX75BP-893-S+



Generic photo used for illustration purposes only
CASE STYLE: HY1238
Connectors Model

SMA-M\F

ZX75BP-893-S+

#### Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Тур.	Max.	Unit
	Center Frequency	-	-	-	892.5	-	MHz
Pass Band	Insertion Loss	F1-F2	870-915	-	0.9	2	dB
	VSWR	F1-F2	870-915	-	1.3	-	:1
Stop Band, Lower	Insertion Loss	DC-F3	DC - 750	20	40	-	dB
	VSWR	DC-F3	DC - 750	-	20	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	1050-1800	20	30	-	dB
	VSWR	F4-F5	1050-1800	-	20	-	:1


Maximum	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	5 W max.


<sup>\*</sup> Passband rating, derate linearly to 3.5W at 85°C ambient.


Permanent damage may occur if any of these limits are exceeded.


### Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1.0	104.63	4103.70	870.0	8.18
500.0	59.74	160.27	872.0	8.07
750.0	40.06	63.36	875.0	7.94
774.0	30.24	52.01	877.0	7.86
797.0	20.15	35.20	880.0	7.76
816.0	10.69	14.75	885.0	7.62
832.0	3.53	3.60	887.0	7.58
870.0	0.93	1.06	890.0	7.52
880.0	0.90	1.09	892.5	7.49
892.5	0.89	1.13	893.0	7.49
893.0	0.89	1.14	895.0	7.46
915.0	0.93	1.21	897.0	7.45
955.0	3.76	4.20	900.0	7.44
975.0	10.80	18.09	903.0	7.45
1005.0	20.84	50.28	905.0	7.45
1040.0	30.18	70.22	907.0	7.47
1050.0	32.61	72.44	908.0	7.48
1500.0	42.84	79.78	910.0	7.51
1700.0	42.09	78.37	912.0	7.54
1800.0	41.87	76.27	915.0	7.62










#### **Features**

- · Low Insertion loss
- · High selectivity
- Good VSWR
- · Connectorized package


#### **Applications**

- Aviation
- · Public cellular network, GSM
- Cellular services
- · Defense systems

#### **Functional Schematic**



#### **Typical Frequency Response**



#### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.


B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

#### **Coaxial Connections**

INPUT	SMA-MALE		
OUTPUT	SMA-FEMALE		

#### **Outline Drawing**



#### Outline Dimensions (inch )

Α	В	С	D	Ε	F	G
1.20	.75	.46	1.18	.04	.17	1.00
30.48	19.05	11.68	29.97	1.02	4.32	25.40
Н	J	K	L	М	Ν	Wt.
H <b>.50</b>	J <b>.35</b>	K . <b>18</b>	L .21	M <b>2.05</b>	N . <b>106</b>	Wt. grams

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp