Coaxial

Coaxial-Ceramic Resonator Filters and Multiplexers

DC to 6 GHz 50Ω

The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



Product Overview

Mini-Circuits' Coaxial-Ceramic Resonator filters offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency

All our coaxial-ceramic resonator filters are built with rugged construction. Excellent repeatability across units is achieved through precise tuning and process control.

Key Features

Feature	Advantages
Low insertion loss	Low signal loss results in better SNR in signal chain
Fast roll-off	Higher selectivity results in better adjacent channel rejection and dynamic range
Wide stop band	Wide spur-free stopband results in better receiver sensitivity
Excellent power handling	Well suited for transmitter applications
Rugged Construction	These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles
Small Size	Very well suited for high performance applications where size is a constraint.
Temperature stability	Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Bandpass Filter

 50Ω 1120 to 1340 MHz

ZX75BP-B1230-S+



Generic photo used for illustration purposes only CASE STYLE: HY1238

Electrical Specifications at 25°C


Electrical opecinications at 25 o							
Parai	meter	er F# Frequency (MHz) Min. Typ.		Max.	Unit		
	Center Frequency	_	_	_	1230	_	MHz
Pass Band	Insertion Loss	F1-F2	1120 - 1340	_	0.9	1.8	dB
	VSWR		1120 - 1340	_	1.3	2.0	:1
		DC-F3	DC - 700	60	70	_	dB
Stop Band, Lower	Insertion Loss	F3-F4	700 - 830	40	45	_	dB
Stop Band, Lower		F4-F5	830 - 940	20	25	_	dB
	VSWR	DC-F5	DC - 940	_	20	_	:1
		F6-F7	1750 - 2050	25	30	_	dB
Stop Band, Upper	Insertion Loss	F7-F8	2050 - 2400	45	50	_	dB
Stop Barid, Opper	F7-F8	2400 - 3500	_	20	_	dB	
	VSWR		1750 - 3500	–	20	_	:1

Maximum Ratings				
Operating Temperature	-40°C to 85°C			
Storage Temperature	-55°C to 100°C			
RF Power Input	5 W			

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nSec)
1	102.57	135083.82	1120	3.90
100	102.27	2105.31	1130	3.73
210	99.30	757.65	1140	3.59
400	110.78	292.42	1150	3.46
700	72.56	123.97	1160	3.35
830	50.25	93.78	1170	3.25
940	30.03	64.33	1180	3.15
985	20.15	43.50	1190	3.06
1054	3.12	3.43	1200	2.98
1100	0.86	1.16	1210	2.91
1120	0.81	1.20	1220	2.86
1230	0.76	1.32	1230	2.83
1340	0.72	1.14	1240	2.80
1320	0.69	1.10	1250	2.77
1600	19.16	55.68	1260	2.76
1640	22.47	64.52	1270	2.75
1750	30.59	79.43	1280	2.74
2050	57.32	87.17	1290	2.75
2400	70.71	83.44	1300	2.75
3500	44.37	43.56	1340	2.85



- Notes

 A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

....Mini-Circuits்

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

FREQUENCY (MHz)

FREQUENCY (MHz)


Features

- · Low insertion loss
- High selectivity
- · Connectorized package


Applications

- · Aeronautical navigation
- Mobile radio
- · Radar system
- Aviation

Functional Schematic



Typical Frequency Response




+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Coaxial Connections

PORT - 1	SMA-MALE
PORT - 2	SMA-FEMALE

Outline Drawing



Outline Dimensions (inch)

G	F	E	D	C	B	A
1.00	.17	. 04	1.18	.46	.75	1.20
25.40	4.32	1.02	29.97	11.68	19.05	30.48
Wt.	N	M	L	K	J	H
grams	. 106	2.05	.21	.18	.35	. 50
35.0	2.69	52.07	5.28	4.57	8.89	12.70

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp