

CASE STYLE: HQ1157

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

REV. B
M174392
EDR-9070AU
BPF-A113+
URJ/RAV
190606
Page 1 of 1

Surface Mount Band Pass Filter

BPF-A113+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	96.50	95.50	99.30	0.47	0.63	0.76	0.48	0.63	0.76
10	92.11	89.47	89.30	0.53	0.67	0.79	0.50	0.65	0.77
30	88.11	97.06	84.63	0.35	0.44	0.51	0.37	0.44	0.50
40	85.82	86.02	95.56	0.28	0.34	0.39	0.30	0.35	0.39
60	85.67	89.78	88.45	0.17	0.21	0.23	0.19	0.23	0.26
70	71.99	71.64	73.44	0.13	0.16	0.20	0.13	0.17	0.20
80	59.00	58.67	58.29	0.11	0.15	0.16	0.11	0.15	0.18
85	51.46	51.22	50.88	0.11	0.14	0.16	0.10	0.15	0.17
95	32.74	32.36	31.92	0.21	0.27	0.31	0.19	0.26	0.31
100	19.53	19.12	18.67	0.61	0.75	0.89	0.61	0.76	0.88
102	12.91	12.56	12.17	1.32	1.61	1.88	1.39	1.69	1.94
105	3.80	3.95	3.99	8.27	9.20	10.07	9.43	10.62	11.60
108	1.89	2.16	2.33	19.18	19.95	20.88	18.08	18.13	18.21
110	1.70	1.96	2.13	33.37	33.83	34.60	18.70	18.17	17.81
113	1.65	1.88	2.04	16.74	17.37	18.12	15.65	15.98	16.43
115	1.62	1.86	2.02	17.25	18.27	19.43	17.21	18.31	19.73
118	1.68	1.95	2.16	20.42	19.54	18.81	27.26	25.13	23.50
120	1.87	2.17	2.37	15.95	16.27	16.74	17.37	17.63	17.98
125	5.91	6.71	7.44	5.41	5.27	5.00	4.53	4.44	4.27
127	11.18	11.92	12.62	2.39	2.51	2.53	1.97	2.10	2.15
130	18.65	19.19	19.71	1.19	1.33	1.41	0.99	1.12	1.21
140	35.18	35.45	35.70	0.49	0.57	0.64	0.43	0.51	0.57
155	49.41	49.37	49.68	0.27	0.34	0.39	0.24	0.31	0.36
160	52.89	53.03	53.26	0.24	0.30	0.35	0.22	0.29	0.33
170	58.83	58.94	58.86	0.18	0.25	0.30	0.18	0.24	0.28
180	63.57	63.68	62.97	0.17	0.23	0.27	0.15	0.21	0.25
190	66.20	66.36	66.63	0.15	0.21	0.25	0.12	0.18	0.22
200	71.13	71.83	69.54	0.13	0.19	0.23	0.11	0.18	0.21
210	74.22	72.95	74.65	0.11	0.17	0.21	0.10	0.16	0.20
220	78.04	79.11	74.38	0.11	0.16	0.21	0.08	0.16	0.20
230	77.41	79.67	76.43	0.09	0.15	0.19	0.09	0.16	0.20
240	84.17	82.55	82.59	0.08	0.14	0.19	0.08	0.14	0.20
250	83.35	85.79	85.49	0.09	0.14	0.19	0.07	0.14	0.18
260	87.73	88.96	89.72	0.07	0.14	0.18	0.07	0.14	0.18
270	81.59	86.77	92.44	0.07	0.13	0.17	0.06	0.13	0.17
280	87.86	91.57	84.22	0.08	0.14	0.18	0.06	0.13	0.18
290	86.98	91.06	91.59	0.07	0.13	0.17	0.05	0.13	0.17
300	82.28	85.40	89.63	0.08	0.14	0.18	0.05	0.13	0.17
400	87.03	93.14	93.85	0.05	0.13	0.18	0.03	0.14	0.19
500	85.39	86.57	90.43	0.05	0.15	0.21	0.03	0.15	0.20
600	93.59	83.59	85.02	0.06	0.16	0.23	0.02	0.18	0.23
700	86.39	85.28	95.48	0.09	0.20	0.29	0.03	0.21	0.28
800	88.12	93.04	92.29	0.10	0.22	0.31	0.06	0.24	0.32
900	85.55	90.14	89.45	0.12	0.25	0.34	0.06	0.28	0.34
1000	95.52	91.02	86.09	0.12	0.25	0.36	0.06	0.30	0.37
1100	77.58	77.44	81.62	0.16	0.30	0.40	0.09	0.31	0.38
1200	86.47	98.96	85.90	0.14	0.30	0.40	0.11	0.35	0.41
1300	83.53	87.14	83.72	0.19	0.34	0.44	0.14	0.36	0.44
1400	79.14	76.82	78.86	0.20	0.36	0.48	0.15	0.38	0.45
1500	81.64	82.02	83.23	0.22	0.38	0.49	0.15	0.39	0.46
1600	77.52	77.27	81.29	0.19	0.36	0.48	0.16	0.40	0.48
1700	71.32	69.17	71.95	0.22	0.41	0.52	0.16	0.41	0.48
1800	78.61	73.18	73.79	0.24	0.42	0.55	0.18	0.43	0.51
1900	76.24	76.89	70.80	0.23	0.44	0.55	0.18	0.44	0.52
2000	66.98	65.98	66.68	0.23	0.41	0.55	0.17	0.45	0.54

REV. X1

BPF-A113+

091220

Page 1 of 2



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Surface Mount Band Pass Filter

BPF-A113+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
108.00	61.87	61.07	60.08
108.25	60.40	59.64	58.71
108.50	59.00	58.21	57.53
108.75	57.99	57.34	56.60
109.00	57.03	56.39	55.74
109.25	56.14	55.51	54.84
109.50	55.30	54.55	54.19
109.75	54.59	54.01	53.58
110.00	53.81	53.06	52.67
110.25	53.07	52.47	52.00
110.50	52.72	52.10	51.72
110.75	51.92	51.61	50.99
111.00	51.41	50.98	50.57
111.25	50.93	50.56	50.03
111.50	50.48	49.96	49.73
111.75	49.69	49.36	49.17
112.00	49.27	48.95	48.74
112.25	48.97	48.70	48.38
112.50	48.38	48.22	48.22
112.75	48.12	48.21	48.00
113.00	47.83	47.70	47.66
113.25	47.59	47.48	47.62
113.50	47.36	47.35	47.54
113.75	47.27	47.29	47.31
114.00	46.81	46.96	46.99
114.25	47.05	47.17	47.20
114.50	46.96	47.12	47.16
114.75	47.06	47.06	47.17
115.00	46.98	47.11	47.26
115.25	47.36	47.25	47.52
115.50	47.12	47.31	47.37
115.75	47.46	47.43	47.46
116.00	47.37	47.56	47.48
116.25	47.77	47.62	47.62
116.50	47.80	47.79	47.76
116.75	48.13	47.86	48.10
117.00	48.13	48.08	48.15
117.25	48.35	48.18	48.31
117.50	48.35	48.43	48.41
117.75	48.50	48.64	48.53
118.00	48.57	48.80	48.63

REV. X1
BPF-A113+
091220
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



Typical Performance Curves



REV. X1
BPF-A113+
091220
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions

HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F83

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR HQ1157 CASE STYLE, rf PIN CONNECTION




NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025"±.002". COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	HB (RAVON)	12 JUN 2008
	CHECKED	RZ (RAVON)	12 JUN 2008
	APPROVED	HH (RAVON)	12 JUN 2008



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, rf, HQ1157, TB-363+, 50 OHM


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

Mini-Circuits®


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-227	C
FILE:	98PL227	SCALE:	2:1
SHEET:	1 OF 1		

Evaluation Board and Circuit



TB-363+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D