

Coaxial

Voltage Controlled Oscillator

ZX95-2705-S+

Wide Band 1950 to 2705 MHz

Features

- linear tuning characteristics
- low pushing
- protected by US patent 6,790,049

Applications

- r & d
- lab
- instrumentation
- wireless communications
- cable TV



Generic photo used for illustration purposes only
CASE STYLE: GB956

| Connectors | Model |
|------------|--------------|
| SMA | ZX95-2705-S+ |

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications


| MODEL NO. | FREQ. (MHz) | | POWER OUTPUT (dBm) | PHASE NOISE dBc/Hz SSB at offset frequencies, kHz | | | | TUNING | | | | NON HARMONIC SPURIOUS (dBc) | HARMONICS (dBc) | | PULLING pk-pk @ 12 dB (MHz) | PUSHING (MHz/V) | DC OPERATING POWER | | |
|--------------|-------------|------|--------------------|---|-----|------|------|--------|-------------------|----------------------|---------------|-----------------------------|---------------------------------|------|-----------------------------|-----------------|--------------------|-------------|--------------|
| | Min. | Max. | | Typ. | 1 | 10 | 100 | 1000 | VOLTAGE RANGE (V) | SENSI-TIVITY (MHz/V) | PORT CAP (pF) | | 3 dB MODULATION BANDWIDTH (MHz) | Typ. | | | Max. | Vcc (volts) | Current (mA) |
| ZX95-2705-S+ | 1950 | 2705 | +8.5 | -64 | -90 | -112 | -132 | 0.5 | 10 | 98-161 | 20 | 300 | -90 | -29 | -15 | 18 | 3 | 8.5 | 30 |

Maximum Ratings

| | |
|--------------------------------------|----------------|
| Operating Temperature | -55°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| Absolute Max. Supply Voltage (Vcc) | 9.5V |
| Absolute Max. Tuning Voltage (Vtune) | 12V |
| All specifications | 50 ohm system |

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



Outline Dimensions (inch/mm)

| A | B | C | D | E | F | G | H | J | K | L | M | N | P | Q | R | S | T | wt. |
|-------|-------|-------|-------|------|------|------|-------|------|------|------|------|------|-------|-------|------|------|------|-------|
| 1.20 | .75 | .46 | 1.18 | .04 | .38 | .38 | .57 | .18 | .33 | .21 | .22 | .08 | 1.00 | .50 | .35 | .18 | .106 | grams |
| 30.48 | 19.15 | 11.61 | 30.07 | 1.02 | 9.53 | 9.53 | 14.43 | 4.62 | 8.31 | 5.28 | 5.59 | 2.03 | 25.40 | 12.70 | 8.89 | 4.57 | 2.69 | 35.0 |

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp









www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Performance Data & Curves*

ZX95-2705-S+

| V TUNE | TUNE SENS (MHz/V) | FREQUENCY (MHz) | | | POWER OUTPUT (dBm) | | | Icc (mA) | HARMONICS (dBc) | | | FREQ. PUSH (MHz/V) | FREQ. PULL (MHz) | PHASE NOISE (dBc/Hz) at offsets | | | | FREQ OFFSET (KHz) | PHASE NOISE at 2325 MHz (dBc/Hz) |
|--------|-------------------|-----------------|--------|--------|--------------------|-------|-------|----------|-----------------|-------|-------|--------------------|------------------|---------------------------------|-------|--------|--------|-------------------|----------------------------------|
| | | -55°C | +25°C | +85°C | -55°C | +25°C | +85°C | | F2 | F3 | F4 | | | 1kHz | 10kHz | 100kHz | 1MHz | | |
| 0.00 | 158.73 | 1690.1 | 1660.5 | 1641.5 | 8.18 | 7.96 | 7.25 | 22.32 | -23.9 | -42.5 | -39.5 | 1.62 | 29.07 | -67.78 | -88.8 | -109.2 | -129.2 | 1.0 | -64.74 |
| 0.50 | 148.04 | 1768.9 | 1739.8 | 1721.1 | 8.25 | 8.25 | 7.60 | 22.44 | -24.7 | -37.1 | -38.7 | 1.91 | 26.53 | -67.64 | -90.3 | -110.9 | -130.9 | 2.0 | -72.99 |
| 1.00 | 143.39 | 1843.7 | 1813.9 | 1794.4 | 8.46 | 8.34 | 7.80 | 22.56 | -25.9 | -33.3 | -37.4 | 2.20 | 25.74 | -68.48 | -90.4 | -111.4 | -131.5 | 3.5 | -79.15 |
| 2.00 | 151.07 | 1989.5 | 1956.4 | 1935.3 | 8.55 | 8.49 | 8.23 | 22.82 | -30.5 | -28.6 | -39.3 | 2.40 | 24.14 | -65.52 | -90.6 | -111.6 | -131.9 | 6.0 | -85.00 |
| 2.50 | 160.90 | 2071.6 | 2031.9 | 2008.5 | 8.92 | 8.56 | 8.12 | 22.96 | -34.1 | -28.7 | -41.8 | 2.31 | 24.11 | -64.30 | -89.7 | -111.3 | -131.6 | 8.5 | -88.66 |
| 3.00 | 153.86 | 2152.2 | 2112.3 | 2085.6 | 9.28 | 8.75 | 8.34 | 23.15 | -42.2 | -28.8 | -38.0 | 2.74 | 26.86 | -63.43 | -89.8 | -111.3 | -131.6 | 10.0 | -90.34 |
| 3.50 | 148.29 | 2228.6 | 2189.3 | 2162.3 | 9.36 | 8.97 | 8.50 | 23.33 | -42.0 | -28.4 | -36.5 | 2.77 | 20.92 | -63.81 | -90.3 | -111.6 | -132.2 | 20.8 | -97.42 |
| 4.00 | 144.46 | 2301.4 | 2263.4 | 2238.3 | 9.32 | 9.13 | 8.63 | 23.48 | -37.9 | -28.4 | -35.2 | 2.73 | 13.47 | -65.36 | -90.7 | -112.1 | -132.6 | 35.5 | -102.35 |
| 4.50 | 138.12 | 2371.0 | 2335.6 | 2311.0 | 9.34 | 9.05 | 8.59 | 23.56 | -38.9 | -27.6 | -36.4 | 2.81 | 13.95 | -65.09 | -90.3 | -111.9 | -132.4 | 60.7 | -106.97 |
| 5.00 | 129.46 | 2438.6 | 2404.7 | 2380.1 | 9.25 | 9.00 | 8.66 | 23.59 | -38.3 | -28.0 | -37.1 | 2.86 | 7.80 | -64.71 | -89.6 | -111.3 | -131.8 | 86.7 | -110.45 |
| 5.50 | 125.84 | 2502.6 | 2469.4 | 2447.1 | 9.04 | 8.92 | 8.59 | 23.62 | -33.2 | -28.2 | -38.9 | 2.59 | 13.76 | -66.96 | -90.9 | -111.8 | -132.3 | 100.0 | -111.71 |
| 6.00 | 118.61 | 2562.8 | 2532.4 | 2510.9 | 8.97 | 8.83 | 8.42 | 23.66 | -29.2 | -28.8 | -38.0 | 2.37 | 15.57 | -66.45 | -91.6 | -112.6 | -133.0 | 123.9 | -113.71 |
| 6.50 | 110.74 | 2621.3 | 2591.7 | 2569.8 | 8.79 | 8.65 | 8.36 | 23.63 | -26.7 | -30.2 | -36.5 | 2.42 | 16.33 | -65.49 | -91.0 | -112.5 | -132.7 | 177.0 | -116.86 |
| 7.00 | 106.65 | 2676.7 | 2647.0 | 2626.5 | 8.62 | 8.52 | 8.21 | 23.62 | -25.0 | -31.7 | -37.1 | 2.39 | 18.92 | -65.92 | -91.3 | -112.6 | -132.9 | 211.6 | -118.48 |
| 7.50 | 101.22 | 2728.6 | 2700.4 | 2680.3 | 8.50 | 8.39 | 8.07 | 23.62 | -23.5 | -31.5 | -38.4 | 2.37 | 9.44 | -67.06 | -91.6 | -112.8 | -133.1 | 302.4 | -121.60 |
| 8.00 | 92.63 | 2778.0 | 2751.0 | 2730.3 | 8.39 | 8.21 | 7.99 | 23.60 | -22.4 | -30.7 | -40.4 | 2.52 | 10.60 | -66.07 | -90.7 | -112.3 | -132.5 | 361.5 | -123.19 |
| 8.50 | 90.89 | 2825.4 | 2797.3 | 2778.1 | 8.20 | 8.19 | 7.89 | 23.57 | -21.5 | -30.9 | -42.6 | 2.55 | 17.71 | -66.04 | -91.2 | -112.5 | -132.7 | 507.5 | -126.20 |
| 9.00 | 83.14 | 2869.1 | 2842.7 | 2823.6 | 8.15 | 8.01 | 7.75 | 23.57 | -20.5 | -30.9 | -43.7 | 2.49 | 9.25 | -65.58 | -92.1 | -113.2 | -133.4 | 606.7 | -127.80 |
| 9.50 | 80.72 | 2910.8 | 2884.3 | 2866.0 | 8.04 | 8.04 | 7.70 | 23.54 | -19.8 | -31.2 | -45.4 | 2.45 | 12.52 | -66.04 | -92.6 | -113.5 | -133.8 | 712.4 | -129.22 |
| 10.00 | 72.28 | 2949.4 | 2924.7 | 2905.8 | 7.94 | 7.86 | 7.67 | 23.52 | -19.3 | -32.3 | -46.0 | 2.46 | 16.37 | -67.62 | -92.9 | -113.4 | -133.7 | 1000.0 | -132.23 |

*at 25°C unless mentioned otherwise



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

